




NOTES:

- 1 MATERIAL: ELECTROLYTIC COPPER ALLOY, TYPE 110 ETP, ASTM B187
- 2 MINIMUM SURFACE FINISH 125 MICRONS REQUIRED ON ALL SURFACES UNLESS OTHERWISE NOTED



REVISIONS					
ZONE	REV.	DESCRIPTION	DRAWN BY	DATE	APPR.
F5	A	ADD THE NOTE # 1 & #2 ABOUT THE MATERIAL & THE SURFACE FINISH	J. CLICHE	2014-12-09	J.V.



ITEM NO.	QTY	DRAWING NO.	PART NO.	DESCRIPTION	NOTE / MATL
1	1	S-1001-4646		CONNECTOR 3/4-12 UN-2A	COPPER

PARTS LIST

GENERAL TOLERANCES (UNLESS OTHERWISE SPECIFIED)

X.	± 0.040
.X	± 0.020
.XX	± 0.010
.XXX	± 0.004
ANGLES	$\pm 0.25^\circ$
RADIUS	± 0.010

REMOVE BURRS AND BREAK SHARP EDGES

DIMENSIONS ARE IN INCHES (UNLESS OTHERWISE SPECIFIED)

ElectroComposites
solid HV bushings solution

TITLE: SHORT CONNECTOR 3/4-12 UN WITH FEMALE $\phi 5/8" \times 1.00"$

DRAWN BY: I. LÉVEILLÉ	DATE: 2008/01/28	FORMAT A	CAGE CODE	DRAWING NO. S-1001-4646	REVISION A
CHECK BY:		PROJECTING:		GENERATED BY: SolidWorks 2013	SHEET 1 of 1
PROJECT MANAGER:		SCALE 1 : 2			

This drawing is the proprietary property of Electro Composites (2008) ULC, not part of the public domain, and is issued with the express understanding and agreement that it is not to be reproduced or copied in whole or in part or issued for furnishing information to others, or used directly or indirectly, in any way detrimental to the interest of Electro Composites (2008) ULC and is to be returned upon request by Electro Composites (2008) ULC. All Rights Reserved.