

**NOTE:** FOR INSTRUCTION SHEET SCROLL DOWN TO NEXT SHEET

**NOTES:**

1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
2. BOX VOLUME: 42 IN<sup>3</sup> [688.2 CM<sup>3</sup>]
3. ACCEPTS ALL 4-11/16" COVERS, 707RAC & 709 PARTITIONS, ALL SOLD SEPARATELY
4. UL LISTED
5. KNOCKOUTS IN LOCATION "A" ARE ACCESSIBLE FOR 5-1/2" [140] & 6" [152.4] STUDS ONLY

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
(1/2"-3/4") TKO®	B, C, D, E	3
(1/2"-3/4") TKO®	A (SEE NOTE 5)	3
1/2" KO	A (SEE NOTE 5)	1

**LIST OF PARTS**

DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDE	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED
FAR SIDE SUPPORT	STEEL	GALVANIZED
STUD BRACKET	STEEL	GALVANIZED

257HWP CUS

SYMBOL	REVISION DESCRIPTION	APP	DATE
	INITIAL RELEASE	J.R.	06/22/2015

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE: **4-11/16" SQUARE WELDED BOX 2-1/8" DEEP WITH RAISED GROUND, STUD BRACKET, AND FAR SIDE SUPPORT**

TOLERANCE UNLESS OTHERWISE SPECIFIED

.XX DECIMAL ±.015  
.XXX DECIMAL ±.005  
ANGLE ±2°

**RACO**

South Bend, Indiana

DRAWN BY:

J.R.

APP. BY:

N.S.

DATE:

06/22/2015

SCALE:

1:3


257HWP DIMENSION SHEET FOR CAT. NO.

SIZE:

**A**


# Instructions for using the RACO® Universal Box Stabilizer

## 1-1/2" Deep Boxes




Bend center tab as shown

For 2-1/2" deep studs




Bend center tab as shown - 2 places

For 3-1/2" deep studs




Bend center tab as shown

For 3-5/8" deep studs



Bend center tab as shown

For 4" deep studs



Bend both tabs as shown


For 5-1/2" deep studs




Bend both tabs as shown

For 6" deep studs


## 2-1/8" Deep Boxes



Comes preset




Bend center tab as shown - 2 places




Bend center tab as shown



Bend center tab as shown



Bend both tabs as shown



Bend both tabs as shown

**NOTICE: Bottom knockouts are NOT usable with the FS support.**