



- NOTES:**
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. BOX VOLUME: 42 IN³ [688.2 CM³]
 3. ACCEPTS ALL 4-11/16" COVERS, 707RAC & 709 PARTITIONS, ALL SOLD SEPARATELY
 4. UL LISTED

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
1/2"	A	1
(1/2"-3/4") TKO®	A	3
1"	B, C, D, E	2

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDE	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED

258 CUS

SYMBOL	REVISION DESCRIPTION	APP	DATE
	INITIAL RELEASE	K.K.	06/22/2015

258

DIMENSION SHEET FOR CAT. NO.

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
**4-11/16" SQUARE WELDED BOX
 2-1/8" DEEP WITH RAISED
 GROUND**

TOLERANCE UNLESS OTHERWISE SPECIFIED

.XX DECIMAL ±.015
 .XXX DECIMAL ±.005
 ANGLE ±2°

RACO

South Bend, Indiana

DRAWN BY:	K.K.
APP. BY:	N.S.
DATE:	06/22/2015

SCALE:
 1:3

SIZE:

A