


CAT. #	SIZE	A	B	C	D	E	F	G	H	J	UNS THREAD
2922RT	1/2"	1.04 [26.4]	2.60 [66.0]	1.09 [27.6]	0.73 [18.5]	0.72 [18.3]	0.86 [21.8]	0.68 [17.3]	0.72 [18.3]	1.41 [36.0]	0.858-14UNS
2923RT	3/4"	1.29 [32.8]	2.79 [70.9]	1.39 [35.3]	0.94 [23.9]	0.94 [23.9]	1.09 [27.7]	0.93 [23.6]	0.80 [20.3]	1.50 [38.1]	1.087-14UNS
2924RT	1"	1.54 [39.1]	2.76 [70.1]	1.64 [41.7]	1.17 [29.7]	1.18 [30.0]	1.32 [33.5]	1.15 [29.2]	0.79 [20.1]	1.61 [40.9]	1.331-18UNS
2925RT	1-1/4"	1.93 [49.0]	3.87 [98.3]	2.03 [51.6]	1.54 [39.1]	1.54 [39.1]	1.70 [43.2]	1.48 [37.6]	0.93 [23.6]	2.51 [63.8]	1.701-14UNS
2926RT	1-1/2"	2.14 [54.4]	3.93 [99.8]	2.29 [58.2]	1.78 [45.2]	1.78 [45.2]	1.94 [49.3]	1.70 [43.1]	0.95 [24.1]	2.49 [63.2]	1.933-14UNS
2928RT	2"	2.63 [66.8]	4.05 [102.9]	2.78 [70.6]	2.24 [56.9]	2.24 [56.9]	2.43 [61.7]	2.16 [54.9]	1.00 [25.4]	2.53 [64.3]	2.398-14UNS
2950RT	2-1/2"	3.40 [86.4]	5.69 [144.5]	3.62 [91.9]	2.91 [73.9]	2.91 [73.9]	3.15 [80.0]	2.79 [70.9]	1.32 [33.5]	3.71 [94.2]	3.142-11.5UNS
2952RT	3"	4.05 [102.9]	6.27 [159.3]	4.26 [108.2]	3.55 [90.2]	3.55 [90.2]	3.77 [95.8]	3.48 [88.4]	1.32 [33.5]	4.29 [109.0]	3.776-11.5UNS
2954RT	3-1/2"	4.56 [115.8]	6.35 [161.3]	4.78 [121.4]	4.04 [102.6]	4.04 [102.6]	4.29 [109.0]	3.98 [101.0]	1.33 [33.8]	4.38 [111.3]	4.276-11.5UNS
2956RT	4"	5.06 [128.5]	6.50 [165.1]	5.31 [134.9]	4.54 [115.3]	4.54 [115.3]	4.79 [121.7]	4.49 [114.0]	1.33 [33.8]	4.55 [115.6]	4.776-11.5UNS

TIGHTENING TORQUE			
(SEE CLAUSES 6.2.1 8.17.2.1 8.27.2.1, 8.28.2.2, and 8.28.2.5.)			
TRADE SIZE OF FITTING	METRIC DESIGNATOR	TIGHTENING TORQUE	
		N-m	(lbf-in)
1/4a	10	19.8	175
3/8	12	22.6b	200
1/2	16	33.9	300
3/4	21	56.5	500
1	27	79.1	700
1-1/4	35	113	1000
1-1/2	41	136	1200
2	53	181	1600
2-1/2	63	181	1600
3	78	181	1600
3-1/2	91	181	1600
4	103	181	1600

a APPLIES TO FLEXIBLE CORD FITTINGS ONLY  
b A 3/8 (12) TRADE-SIZE FITTING FOR USE WITH LIQUID-TIGHT FLEXIBLE METAL CONDUIT SHALL BE TIGHTENED WITH A TORQUE OF 26.5 N-M (235 LBF-IN).

REVISIONS			
REV.	DATE	DESCRIPTION	BY:
-	11-13-20	INITIAL RELEASE OF DRAWING	VS



- NOTES:**
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS].
  2. LOCKNUT SHALL BE HAND-TIGHTENED AND THEN FURTHER TIGHTENED 1/4 TURN WITH A HAMMER AND A FLAT BLADED SCREWDRIVER OR BY AN EQUIVALENT METHOD.
  3. RAIN TIGHT.
  4. cULus LISTED.

DESCRIPTION	MATERIAL	FINISH
SEAL RING	POLYPROPYLENE	-
METAL RING	STEEL	ZINC
RING	STEEL	ZINC
COMPRESSION NUT	STEEL	ZINC
COUPLING BODY	STEEL	ZINC

**LIST OF PARTS**

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE: **RainTight Compression Coupling**

TOLERANCE UNLESS OTHERWISE SPECIFIED .XX DECIMAL ±.015 .XXX DECIMAL ±.005 ANGLE ±2°			DRAWN BY:	VS	SCALE:	SIZE:
			APP. BY:	N.S.		
	DATE:	11-13-20	1:1			