



CATALOG NUMBER S025023S2010
GROUND FITTING Y-CLEVIS
LINE FITTING ANSI_52-5_BALL
LINE END RING N/A
GROUND END RING N/A

MECHANICAL CHARACTERISTICS
SPECIFIED MECHANICAL LOAD 25000 POUNDS (111 KN)
ROUTINE TEST LOAD RATING 12500 POUNDS (55.5 KN)

MECHANICAL CHARACTERISTICS
WEIGHT 6.5 LBS (2.9 KG)
OF SHEDS 22
WEATHERSHED SPACING 1.08 IN (27 MM)
CORE DIAMETER 0.93 IN (23 MM)
SECTION LENGTH 35.4 IN (899 MM)
POLYMER LENGTH 23.66 IN (600 MM)
DRY ARCING DISTANCE 23.7 IN (601 MM)
LEAKAGE DISTANCE 60 IN (1524 MM)

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH ANSI C29.11-1989
60 Hz DRY FLASHOVER 250 kV
60 Hz WET FLASHOVER 235 kV
POSITIVE IMPULSE CRITICAL FLASHOVER 415 kV
NEGATIVE IMPULSE CRITICAL FLASHOVER 395 kV

ELECTRICAL CHARACTERISTICS IN ACCORDANCE WITH IEC-383
60 Hz WET WITHSTAND (1 MINUTE) 175 kV
IMPULSE POSITIVE WITHSTAND 370 kV
IMPULSE NEGATIVE WITHSTAND 355 kV

SILICONE RUBBER HOUSING 3MM MINIMUM WALL THICKNESS OVER CORE ROD

Program Revision
2016.10.21.12.08.31
REV DATE 03/08/07

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.



HUBBELL® POWER SYSTEMS

TITLE
QUADRI*SIL INS
SUSPENSION ASSEMBLY

SIZE S	DWG NO. PSXIT-SX	CAT / PART / ASSY NO. S025023S2010	REV 1
DO NOT SCALE THIS DRAWING	DRN BY NON	DATE 11/26/02	SHEET 1 OF 1