

# PARALLEL CLAMP

## Type CP

for Two Copper Cables





Fig. 2



Type CP - Fig. 1

A parallel clamp adaptable for use as an oblique tap or parallel connector. Body is cast of high copper alloy, and the oval-shank bolts, nuts, and lockwashers are of Durium, thus providing a corrosion resistant assembly. Ample contact surface insures full conductivity without overheating.

For use on ALUMINUM conductors, add -W to catalog number

CABLE SIZES		CATALOG NUMBER	APPROX. SHIP. WT. IN LBS.	FIG. NO.	DIMENSIONS IN INCHES					
A	AA				A	AA	B	H	J	W
# 8 Str. 6 6	# 8 Str. 6 6	CP8C8C	.37	1	.146	.146	17/8	7/16	5/16	15/16
		CP8C8C	.37	1	.184	.146	2	7/16	5/16	15/16
		CP6C6C	.37	1	.184	.184	2	7/16	5/16	15/16
# 4 Str. 4 4	# 8 Str. 6 4	CP4C8C	.43	1	.232	.146	2	1/2	5/16	1
		CP4C6C	.43	1	.232	.184	2	1/2	5/16	1
		CP4C4C	.43	1	.232	.232	2 1/4	5/16	5/16	1 1/4
# 2 Str. 2 2 2	# 8 Str. 6 4 2	CP2C8C	.50	1	.291	.146	2 1/4	5/8	5/16	1 1/4
		CP2C6C	.50	1	.291	.184	2 1/4	5/8	5/16	1 1/4
		CP2C4C	.50	1	.291	.232	2 1/4	5/8	5/16	1 1/4
		CP2C2C	.63	1	.291	.291	2 1/4	7/8	5/8	1 1/4
1/0 1/0 1/0 1/0 1/0	# 8 Str. 6 4 2 1/0	CP258C	.62	1	.373	.146	2 1/4	1 1/16	5/8	1 3/4
		CP256C	.62	1	.373	.184	2 1/4	1 1/16	5/8	1 3/4
		CP254C	.75	1	.373	.232	2 1/2	3/4	5/8	1 3/4
		CP252C	.88	1	.373	.291	2 1/2	3/4	5/8	1 3/4
		CP252S	.88	1	.373	.373	3	1 1/16	5/8	1 3/4
2/0 2/0 2/0 2/0 2/0 2/0 2/0	# 8 Str. 6 4 2 1/0 2/0 2/0	CP268C	.68	1	.416	.146	2 1/4	1 1/16	5/8	1 3/4
		CP266C	.68	1	.416	.184	2 1/4	1 1/16	5/8	1 3/4
		CP244C	.75	1	.416	.232	2 1/2	3/4	5/8	1 3/4
		CP262C	.75	1	.416	.291	2 1/2	3/4	5/8	1 3/4
		CP262S	.88	1	.416	.373	3	1 1/16	5/8	1 3/4
		CP2626	.88	1	.416	.416	3	1 1/16	5/8	1 3/4
		CP276C	.75	1	.470	.184	2 1/2	1 1/16	5/8	1 3/4
		CP274C	.75	1	.470	.232	2 1/2	1 1/16	5/8	1 3/4
3/0 3/0 3/0 3/0 3/0	# 6 Str. 4 2 1/0 2/0 3/0	CP272C	.88	1	.470	.291	2 3/4	1 1/16	5/8	1 3/4
		CP272S	.88	1	.470	.373	3	1 1/16	5/8	1 3/4
		CP2726	1.0	1	.470	.416	3	1 1/16	5/8	1 3/4
		CP2727	1.2	1	.470	.470	4	1 1/16	5/8	1 3/4
		CP284C	.88	1	.528	.232	2 1/2	1 1/16	5/8	1 3/4
4/0 4/0 4/0 4/0 4/0 4/0	# 4 Str. 2 1/0 2/0 3/0 4/0	CP282C	1.0	1	.528	.291	2 3/4	1 1/16	5/8	1 3/4
		CP282S	1.2	1	.528	.373	3	1 1/16	5/8	1 3/4
		CP2826	1.4	1	.528	.416	3	1 1/16	5/8	1 3/4
		CP2827	1.5	1	.528	.470	4	1 1/16	5/8	1 3/4
		CP2828	1.6	2	.528	.528	4	1 1/16	5/8	1 3/4
		CP294C	1.0	1	.575	.232	2 1/2	1 1/16	5/8	1 3/4
		CP292C	1.1	1	.575	.291	2 3/4	1 1/16	5/8	1 3/4
		CP292S	1.2	1	.575	.373	3	1 1/16	5/8	1 3/4
250 Mcm 250 Mcm 250 Mcm 250 Mcm 250 Mcm 250 Mcm	# 4 Str. 2 1/0 2/0 3/0 4/0 250 Mcm	CP2926	1.3	1	.575	.416	3	1 1/16	5/8	1 3/4
		CP2927	1.4	2	.575	.470	4	1 1/16	5/8	1 3/4
		CP2928	1.6	2	.575	.528	4	1 1/16	5/8	1 3/4
		CP2929	1.7	2	.575	.575	4	1 1/16	5/8	2 1/4
		CP302S	1.4	1	.630	.373	3	1 1/16	5/8	1 3/4
300 Mcm 300 Mcm 300 Mcm 300 Mcm 300 Mcm 300 Mcm 300 Mcm	1/0 2/0 3/0 4/0 250 Mcm 300 Mcm	CP3026	1.5	1	.630	.416	3	1 1/16	5/8	1 3/4
		CP3027	1.6	2	.630	.470	4	1 1/16	5/8	1 3/4
		CP3028	1.7	2	.630	.528	4	1 1/16	5/8	1 3/4
		CP3029	1.8	2	.630	.575	4	1 1/16	5/8	2 1/4
		CP3030	1.9	2	.630	.630	4	1 1/16	5/8	2 1/4

SHEET 1 OF 3  
**PARALLEL CLAMP**  
 CAT. NO. CP (GEN'L)  
 DRAWN E.O. 6-17-52 CHECKED S.W. 12-10-52  
**BURNDY**  
 Corporation  
 SA-88939