






CAT. NDL  
C107-0573




CAT. NDL  
C107-0574




CAT. NDL  
C107-0575




CAT. NDL  
C107-0576




CAT. NDL  
C107-0580



CAT. NDL  
C107-0579



CAT. NDL  
C107-0578




CAT. NDL  
C107-0577

**INCLUDED HARDWARE**

PART NDL	DESCRIPTION
P001-0967	MACH BOLT, 3/4" X 5-3/4" GR-5
450315	HEX NUT, 3/4"
058331	LDRKASHER, 3/4"

- NOTES-**
1. FINISH, HOT DIP GALVANIZE PER ASTM A153-(LATEST REVISION)
  2. MANUFACTURER TO HAVE IN EFFECT INDUSTRY RECOGNIZED WRITTEN QUALITY CONTROL FOR ALL MATERIALS AND MANUFACTURING PROCESSES.
  3. MAXIMUM INSTALLATION TORQUE RATING FOR RS3500, 300 HELICAL.
  4. ALLS UNLESS OTHERWISE SPECIFIED.
  5. IN COMPLIANCE WITH AWS CODE D1. 1, WITH WELDERS BEING QUALIFIED UNDER SECTION 5, PART C.
  6. MAXIMUM ALLOWABLE TOLERANCE ON HELIX SPACING, ±1/4".
  7. EXTENSIONS MUST BE PROVIDED WITH A HOT FORGE EXPANDED INTEGRAL COUPLING CONNECTION ON ONE END.
  8. COUPLING BOLTS (3 REQUIRED) PER SPEC SAE J429 GRADE 5.



HELIX MUST BE FORMED BY MATCHING METAL DIE (SIDE VIEW OF TRUE HELICAL FORM)

**CHANCE TOLERANCE CHART**

**HUBBEL POWER SYSTEMS**

RS3500.300 EXTENSIONS

SIZE	DRG NO.	REV	DATE
D	SH107-10045	1	11/20/95

REV C