



Ø56 BOLT CIRCLE
8 2.25" DIA BOLTS
EVENLY SPACED





THREADBAR WITH
FORGED/WELDED PUCK



SECTION A-A

SQUARE TUBE FILLED WITH
NONSHRINK GROUT MINIMUM 4000
PSI COMPRESSIVE STRENGTH
PROVIDED BY OTHERS


GRILLAGE NO PILES



GRILLAGE WITH PILES

==NOTES==

1. FINISH: GALVANIZE PER ASTM A123 (LATEST REVISION)
2. SEE SALES DRAWING FOR HARDWARE PACKS. SA1101707 FOR RS4500.337 AND SA1101708 FOR RS 3500.300.
3. MATERIAL:
 - A. PLATE: PLATE STEEL PER ASTM A572 GRD 50
 - B. PILE TUBES: HSS 10X10X1/2 PER ASTM A500 GRD B, MIN 50 KSI
 - C. THREADBAR: 1.5-6UNC-2A THREADED ROD PER AISI 4130 HOT ROLLED STEEL
4. ESTIMATED WEIGHT: 5,500 LBS
 - A. CAN ASSEMBLIES: 380 LBS
 - B. CENTER ASSEMBLY: 3,900 LBS



CHANCE®



HUBBELL POWER SYSTEMS, INC.

12 PILE
GRILLAGE

CONFIDENTIAL: THIS DRAWING AND ITS
CONTENTS ARE CONFIDENTIAL AND THE
EXCLUSIVE PROPERTY OF HUBBELL POWER
SYSTEMS. NO PUBLICATION, DISTRIBUTION, OR
COPIES MAY BE MADE WITHOUT THE WRITTEN
CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL
POWER SYSTEMS UNPUBLISHED ALL RIGHTS
RESERVED UNDER THE COPYRIGHT LAWS.

SIZE	CAT / PART / ASSY NO.	DWG NO.	REV
B	C1102075	SA1102075	A
DO NOT SCALE THIS DRAWING	DRN BY BLJ	DATE 2/10/2022	SHEET 1 OF 1