


- NOTES -

1. LINK MATERIAL: 60-40-18 DUCTILE IRON PER ASTM A536.
2. HARDWARE MATERIAL: STEEL BOLTS AND NUTS PER SAE J429 GRADE 5 AND PINS PER ASTM A325.
3. COTTER KEY MATERIAL: BRASS OR 300 SERIES STAINLESS STEEL.
4. FINISH: HOT DIP GALVANIZED PER ASTM A153.
5. STRENGTH RATING: 15,000LB GUY LOAD.
6. 12" NOMINAL POLE DIAMETER. CLIP POLE BAND LINK ASSEMBLY ALLOWS FOR $\pm 2"$ OF CIRCUMFERENCE ADJUSTMENT.
7. ASSEMBLED AS SHOWN.



CATALOG NUMBER PSC203AF12

CHANCE [®]		HUBBELL [®] HUBBELL POWER SYSTEMS, INC.		
POWER SYSTEMS, INC.		TITLE		
CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION, OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.		LINK STYLE POLE BAND		
SIZE B	CAT / PART / ASSY NO. PSC203AF12	DWG NO. SA203AF12	REV A	
DO NOT SCALE THIS DRAWING	DRN BY TOLIVER	DATE 5/31/22	SHEET 1 OF 1	