



==NOTES==

1. A MINIMUM TENSILE ULTIMATE STRENGTH OF 95 KSI AND A MINIMUM IMPACT STRENGTH OF 15 FT.-LBS. AT -20°F WITH CHАРY V-NOTCH TYPE A SPECIMENS.
2. HOT DIP GALVANIZE PER ASTM A153-(LATEST REVISION).



CHANCE PART NO.	" A "	" B "	" C "	" D "	" E "	" F "	" G "	WT.	BOLT DIA	GRADE
T1100134	1.81	.94	1.13	4.06	2.63	4.19	6.63	6.6	.875	B7
C1100557	2.25	1.19	1.38	5.00	3.31	5.19	8.22	12.0	1.125	B7
C1100558	2.38	1.31	1.50	5.38	3.63	5.70	9.00	16.2	1.25	B7

CHANCE TOLERANCE CHART		HUBBELL POWER SYSTEMS	
CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.			
TITLE SHACKLE SS175, SS200, SS225		SIZE C	DWG NO. SA1100134
CAT / PART / ASSY NO. SEE CHART		REV A	DRN BY MTH DATE 07/18/16 SHEET 01 OF 01