


STRAIN LINK STICKS

CATALOG NO.	TOTAL LENGTH "L"	POLE LENGTH "A"	POLE DIAMETER	JAW OPENING MIN/MAX (in.)	MAX WORKING LOAD (lb.)	APPROX. WEIGHT (lb. / kg.)
H47151	3'2.5"	2'5.5"	1-1/4"	.22/.75	3500	2.59 / 1.2
H47152	4'9"	4'	1-1/4"	.22/.75	3500	3.75 / 1.7
C4000814	7'3"	6'	1-1/4"	.22/.75	3500	5.25 / 2.4
C4000815	9'3"	8'	1-1/4"	.22/.75	3500	6.00 / 2.7
C4000816	11'3"	10'	1-1/4"	.22/.75	3500	6.75 / 3.1
C4000817	13'3"	12'	1-1/4"	.22/.75	3500	7.50 / 3.4
C4000818	15'3"	14'	1-1/4"	.22/.75	3500	8.25 / 3.7
H47161	3'3"	2'	1-1/2"	.44/1.06	6500	4.75 / 2.2
H47162	4'9"	4'	1-1/2"	.44/1.06	6500	5.75 / 2.6
H47163	6'9"	6'	1-1/2"	.44/1.06	6500	6.75 / 3.1
H47164	8'9"	8'	1-1/2"	.44/1.06	6500	7.75 / 3.6
H47165	10'9"	10'	1-1/2"	.44/1.06	6500	8.75 / 4.0
H47166	12'9"	12'	1-1/2"	.44/1.06	6500	9.75 / 4.4
H4717	5'0"	4'	1-1/2"	.72/1.50	6500	9.87 / 4.5
H47171	7'2"	6'	1-1/2"	.72/1.50	6500	11.87 / 5.4
H4718	5'2"	4'	1-1/2"	1.00/2.50	6500	11.12 / 5.1
H47181	7'2"	6'	1-1/2"	1.00/2.50	6500	13.00 / 5.9
H47182	9'2"	8'	1-1/2"	1.00/2.50	6500	15.00 / 6.8
H47183	11'2"	10'	1-1/2"	1.00/2.50	6500	17.00 / 7.7
H47184	13'2"	12'	1-1/2"	1.00/2.50	6500	19.00 / 8.6

TESTED PER OSHA & ASTM F711

<small>CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED. ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.</small>		 HUBBELL® POWER SYSTEMS		
		LINK STICK		
<small>TITLE</small>	<small>SIZE</small> B	<small>DWG NO.</small> SAH4718	<small>CAT / PART / ASSY NO.</small> SEE CHART	<small>REV</small> --
<small>DO NOT SCALE THIS DRAWING</small>	<small>DRN BY</small> RAM	<small>DATE</small> 5/19/14	<small>SHEET 1 OF 1</small>	