




-NOTES-

- MATERIAL:**
BASE: DUCTILE IRON, GALVANIZED PER ASTM A153
END FITTINGS: CAST ALUMINUM
- SEE CHART FOR ULTIMATE STRENGTH RATINGS.
RECOMMENDED MAXIMUM WORKING LOAD IS 50% OF
MINIMUM ULTIMATE RATINGS LISTED.
- CATALOG NUMBERS WITH SUFFIX "-CLHCLH" INCLUDE 4, 1/2 X
2" CAPTIVE CARRIAGE BOLT, EXTERNAL TOOTH LOCKWASHER,
LOCKWASHER, HEX NUT, AND CAPPLUG.


CATALOG NUMBER	"L"	"H"	ULTIMATE STRENGTH RATING (LBS)		
			VERTICAL	LONGITUDINAL	TRANSVERSE
2SBH36CLCL	36.0	5.5	1,200	900	10,000
2SBH42CLCL	42.0	6.3	950	700	10,000
2SBH48CLCL	48.0	7.0	900	500	10,000
2SBH36CLHCLH	36.0	5.5	1,200	900	10,000
2SBH42CLHCLH	42.0	6.3	950	700	10,000
2SBH48CLHCLH	48.0	7.0	900	500	10,000



VIEW A-A



LOADING ORIENTATION (NOTE-2)



CHANCE [®]	HUBBELL [®] HUBBELL POWER SYSTEMS, INC.		
	POWER SYSTEMS, INC.		
TITLE CUTOUT/ARRESTER BRACKET 2 PHASE, 3 POSITION, 15°			
SIZE C	CAT / PART / ASSY NO. SEE CHART	DWG NO. SA2SBH48CLCL	REV A
DO NOT SCALE THIS DRAWING	DRN BY HOEK	DATE 8/17/22	SHEET 1 OF 1

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION, OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.