



==NOTES==

1. BOLT MATERIAL: STEEL CONFORMING TO THE FOLLOWING PROPERTIES: PROPERTIES ARE ACHIEVED:
  - AVERAGE MINIMUM ABSORPTION OF 20J WHEN TESTED AT -20°C PER ASTM A370.
  - MINIMUM BOLT BREAKING STRENGTH OF 28,550 LB. (127 kN) WHEN TESTED PER ASTM F606.
  - UNTHREADED PORTION MUST BE CAPABLE OF BEING BENT (COLD) AROUND A MANDREL WITHOUT CRACKING. MANDREL SIZE IS TO BE TWO TIMES THE DIAMETER OF THE SHANK BEING TESTED.
2. HOT DIP GALVANIZE PER CSA G164-M (LATEST REV.).
3. ALL DIMENSIONS BEFORE GALVANIZING.
4. NUT DIMENSIONS PER ASME/ANSI B18.2.2. NUT MATERIAL SAME AS BOLT MATERIAL. TAP NUT AFTER GALVANIZING PER CD46094.

CATALOG NUMBER	"A"	"B"
PSSE3406CW	6.00"	3.00"
PSSE3408CW	8.00"	4.00"
PSSE3410CW	10.00"	6.00"
PSSE3412CW	12.00"	6.00"
PSSE3414CW	14.00"	6.00"
PSSE3416CW	16.00"	6.00"
PSSE3418CW	18.00"	6.00"
PSSE3420CW	20.00"	6.00"
PSSE3422CW	22.00"	6.00"
PSSE3424CW	24.00"	6.00"

<b>CHANCE</b> ®		<b>HUBBELL</b> ® POWER SYSTEMS, INC.		<b>HUBBELL POWER SYSTEMS, INC.</b>	
TITLE					
<b>SHOULDER EYE BOLTS, 3/4 (CW)</b>					
CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION, OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS, HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	SIZE <b>B</b>	CAT / PART / ASSY NO. <b>SEE CHART</b>	DWG NO. <b>SAPSSE3406CW</b>	REV <b>A</b>	
DO NOT SCALE THIS DRAWING	DRN BY CBW	DATE 10/10/22	SHEET 1 OF 1		