


SECTION "A-A"



C600-0337, T600-0844, V600-0646

ELECTRICAL RATINGS	
CONTINUOUS CURRENT (AMPS)	400
FAULT CURRENT - 15 CYCLES (AMPS)	43,000/*60,000
FAULT CURRENT - 30 CYCLES (AMPS)	30,000/*60,000
MECHANICAL RATINGS	
RECOMMENDED TORQUE (IN.-LB.)	300
MAIN LINE RANGE - MAX.	6-5/8" O.D. BUS
MAIN LINE RANGE - MIN.	3-1/2" O.D. BUS
JUMPER RANGE - MAX.	4/0 GRD. CABLE WITH PLAIN PLUG
JUMPER RANGE - MIN.	#2 GRD. CABLE WITH PLAIN PLUG
WEIGHT	6 lb. / 2.7 kg
ASTM DESIGNATION	TYPE I - CLASS A - GRADE 6 -

<b>CHANCE</b> TOLERANCE CHART  <small>CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.</small>	<b>HUBBELL POWER SYSTEMS</b> <small>Hubbell Power Systems, Inc.</small>	
	TITLE: 3-1/2" TO 6-5/8" BUS BAR CLAMP	
SIZE: C DWG NO.: SA6000337 DO NOT SCALE THIS DRAWING	CAT / PART / ASSY NO.: SEE CHART	REV: -- DRN BY: RAM DATE: 1-10-14 SHEET 1 OF 1