



REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	01/01/01	FOR ONE-PIECE 90-DEGREE PART	7249	DDD	PRL



FOR HARDWARE (YNA32R90-H)	
QTY	DESCRIPTION
2	1/2"-13 X 1.75 LONG HEX HEAD BOLTS, AL.
2	1/2"-13 HEX NUT, ALUMINUM
2	1/2" RESILIENT WASHER
2	1/2" FLATWASHER, ALUMINUM

NOTE:

WHEN HARDWARE IS SPECIFIED THE CATALOG NUMBER SHALL BE FOLLOWED BY "H" TO INCLUDE HARDWARE

ACCOMMODATES

300 Kcmil ACSR 18-1 (.646 DIA.) TO 366.4 Kcmil ACSR 30-7 (.741 DIA.)
 336.4 Kcmil ALUMINUM, (.666 DIA) TO 350 Kcmil ALUMINUM, (.682 DIA)
 395.1 Kcmil 12-7 STR. (.721)-395.2 Kcmil 15-7 STR. (.721) STR.

TO ORDER BURNDY PRODUCTS CALL 1-800-346-4175 MANCHESTER, NH 03109, USA FOR PRODUCT INFO = http://www.fciconnect.com			
90 HYLUG FOR BELOW 230 KV			
ITEM NO: 001395			
CAT NO: YNA32R90			
SCALE:	1:2		
DRAWN BY:	D. DOBRINSKI 01/01/02		
CHECKER:	-- 01/01/01		
DSN APPVL:	J. MICHAUD 01/18/02		
MFG APPVL:	S. HOLLOWAY 01/18/02		
QA APPVL:	J. BRODEUR 01/18/02		
WKT APPVL:	-- 01/01/01	DRAWING NO	
PROD FAM:	--	REV	
PROJECT#	--	SIZE	
DOCUMENT TYPE:	Sales	B	SB214382-01
REL LEVEL:	Released		A
			SHEET 1 OF 1

REV: PE0200