



| | |
|--|---------------------------|
| PSC6003499 - 5H ALL-ANGLE GROUND CLAMP | |
| ASTM Designation | Type I, Class B, Grade 5H |
| Rated Current (15 Cycles) | 47 kA Asymmetrical |
| Recommended Torque | 480 in-lb |
| Main Line Range (Min-Max) | 0.258" Dia - 2.88" Dia |
| Ground Cable Required for 5H | 4/0 |
| Weight | 8.0 lb / 3.6kg |



CHANCE®



HUBBELL POWER SYSTEMS, INC.

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION, OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.

TITLE
ALL-ANGLE GROUND CLAMP

| | | | |
|---------------------------|--|-----------------------------|-----------------|
| SIZE B | CAT / PART / ASSY NO. PSC6003499 | DWG NO. SA6003499 | REV A |
| DO NOT SCALE THIS DRAWING | DRN BY TLK | DATE 3/3/20 | SHEET 1 OF 1 |