


# CATALOG NUMBER

## PSC6003696

ASTM Grade	3H / 5
Rated Current - 15 Cycles	31kA High X/R / 43kA
Required Torque	300 in-lb
Max. Line Range	0.8" Dia
Min. Line Range	0.162" Dia
Jaw Type	Smooth

<b>CHANCE</b> <sup>®</sup>		 <b>HUBBELL POWER SYSTEMS, INC.</b>	
<small>CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION, OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.</small>		TITLE <b>C-TYPE GROUND CLAMP, 0.162"-0.8"</b>	
		SIZE <b>B</b>	CAT / PART / ASSY NO. <b>PSC6003696</b>
DO NOT SCALE THIS DRAWING		DRN BY TLK	DATE 06/23/21
		SHEET 1	OF 1