



CATALOG NUMBERING SYSTEM

POSITION
1 2 3 4 5 6 7 8 9 10 11
C 7 2 0 - 2

POSITION 11
SPECIAL OPTIONS
S - STAINLESS STEEL - NOT AVAILABLE

POSITION 10
MOUNTING BRACKET
BLANK OR Z - NO BRACKET
B - NEMA "B" BRACKET
X - EXTENDED BRACKET
D - "D" BRACKET

POSITION 9
TERMINAL OPTIONS
P - PG CLAMPS (TIN PLATING)
E - SMALL EYEBOLT TERMINALS
L - LARGE EYEBOLT TERMINALS
T - FUSEHOLDER ONLY
(POSITION 10 & 11 BLANK)

POSITION 7 & 8
FUSEHOLDER

POSITION 7 & 8	KV MAX DESIGN	AMPS	AIC ASYM	LOADBREAK RATINGS	
				INDUCTIVE AMPERES	CAPACITIVE AMPERES
11	27	100	8000	100	100
13	27	100	12000	100	100

APPROXIMATE DIMENSIONS
FOR REFERENCE ONLY

CHANCE EC #: 51854 DAC: 08-29-13		HUBBELL POWER SYSTEMS POWER SYSTEMS, INC.	
TITLE CUTOUT, LINKBREAK 125KV BIL			
SIZE D	DWG NO. SA720-2	CAT / PART / ASSY NO. SA720-2	REV A
DO NOT SCALE THIS DRAWING		DRN BY MARTIN DATE 1/30/98	SHEET 01 OF 01

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.