


CATALOG NUMBER	"L"	"A"
GS30012CC2SC	12"	16.5"
GS30018CC2SC	18"	32.5"
GS30024CC2SC	24"	38.5"
GS30030CC2SC	30"	44.5"
GS30036CC2SC	36"	50.5"
GS30042CC2SC	42"	56.5"
GS30048CC2SC	48"	62.5"
GS30054CC2SC	54"	68.5"
GS30060CC2SC	60"	74.5"
GS30072CC2SC	72"	86.5"
GS30078CC2SC	78"	92.5"
GS30084CC2SC	84"	98.5"
GS30090CC2SC	90"	104.5"
GS30096CC2SC	96"	110.5"
GS30108CC2SC	108"	122.5"
GS30120CC2SC	120"	134.5"
GS30144CC2SC	144"	158.5"



- NOTES-
- MATERIAL
CLEVIS AND ROLLER: GALVANIZED DUCTILE IRON
CLEVIS PIN: GALVANIZED STEEL
COTTER KEY: STAINLESS STEEL
 - ULTIMATE LOAD RATING: 30,000 LBS
*RECOMMENDED MAXIMUM WORKING LOAD: 15,000 LBS

CHANCE [®]	HUBBELL [®] HUBBELL POWER SYSTEMS, INC. POWER SYSTEMS, INC.		
	TITLE 30K GUY STRAIN 2-ROLLER SILICONE COATED ROD		
CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION, OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	SIZE C	CAT / PART / ASSY NO. SEE CHART	DWG NO. SAGS30XXCC2SC
DO NOT SCALE THIS DRAWING	DRN BY HOEK	DATE 1/21/21	REV A SHEET 1 OF 1