



RUBBER-INSULATED CABLE		PAPER-INSULATED CABLE				CABLE SIZE	A	B	C	D	E	F	L	M	N
CAT. NO.	FIG. NO.	CAT. NO. (SHORT)	FIG. NO.	CAT. NO. (LONG)	FIG. NO.										
YFS28CR	1	YFS28CP	1	YFS28CPL	2	4/0 STR (.528)	1.34	1.72	2.38	8.94	2.91	1.89	15.69	6.41	8.75
YFS29CR	1	YFS29CP	1	YFS29CPL	2	250 KCMIL (.575)	1.34	1.72	2.38	8.94	2.91	1.89	15.69	6.41	8.75
YFS30CR	1	YFS30CP	1	YFS30CPL	2	300 KCMIL (.630)	1.34	1.84	2.38	8.94	3.22	1.89	15.69	6.78	9.50
YFS31CR	1	YFS31CP	1	YFS31CPL	2	350 KCMIL (.681)	1.34	1.84	2.38	8.94	3.22	1.89	15.69	6.78	9.50
YFS32CR	1	YFS32CP	1	YFS32CPL	2	400 KCMIL (.728)	1.34	1.97	2.38	8.94	3.22	1.89	15.69	7.03	9.50
YFS34CR	1	YFS34CP	1	YFS34CPL	2	500 KCMIL (.814)	1.34	2.72	2.38	8.94	4.03	1.89	15.69	8.84	11.59

CATALOG NO.	INSTALLATION TOOLING (# CRIMPS)									
	DIE INFORMATION		HYDRAULIC						WIRE STRIP LENGTH	
	DIE INDEX	TYPE	Y34A	Y750, PAT750, Y35, Y39	PAT46, Y46	Y45	Y48B	Y60BHU	YFS--CR YFS--CP	YFS--CPL
YFS28--	15	PURPLE DIE SET	--	U28RT (2)	U28RT (2)	U28RT (2)	C28R (2)	L28RT (1)	2.50	3.75
		NEST INDENTOR	A28D (1) Y34PR	U28D-I (1) Y34PR	U28D-I (1) Y34PR	U28D-I (1) Y34PR	C28D (1) Y48PR	--		
YFS29--	16	YELLOW DIE SET	--	U29RT (2)	U29RT (2)	U29RT (2)	C29R (2)	L29RT (1)	2.50	3.75
		NEST INDENTOR	A29D (2) Y34PR	U29D-I (2) Y34PR	U29D-I (2) Y34PR	U29D-I (2) Y34PR	C29D (1) Y48PR	--		
YFS30--	17	WHITE DIE SET	--	U30RT (4)	U30RT (4)	U30RT (4)	C30R (1)	L30RT (1)	2.50	3.75
		NEST INDENTOR	A30D (2) Y34PR	U30D-I (2) Y34PR	U30D-I (2) Y34PR	U30D-I (2) Y34PR	C30D (2) Y48PR	--		
YFS31--	18	RED DIE SET	--	U31RT (4)	U31RT (4)	U31RT (4)	C31R (1)	L31RT (1)	2.50	3.75
		NEST INDENTOR	A31D (2) Y34PR	U31D-I (2) Y34PR	U31D-I (2) Y34PR	U31D-I (2) Y34PR	C31D (1) Y48PR	--		
YFS32--	19	BLUE DIE SET	--	U32RT (4)	U32RT (4)	U32RT (4)	C32R (1)	L32RT (1)	2.50	3.75
		NEST INDENTOR	A32D (2) Y34PR	U32D-I (2) Y34PR	U32D-I (2) Y34PR	U32D-I (2) Y34PR	C32D (2) Y48PR	--		
YFS34--	20	BROWN DIE SET	--	U34RT (4)	U34RT (4)	U34RT (4)	C34R (2)	L34RT (2)	3.25	4.50
		NEST INDENTOR	A34D (2) Y34PR	U34D-I (2) Y34PR	U34D-I (2) Y34PR	U34D-I (2) Y34PR	C34D (2) Y48PR	--		

NOTES:

- 1 WHEN FURNISHED WITHOUT RUBBER INSULATING SLEEVE 'C' IS TAKEN OFF CAT. NO; EXAMPLE YFS29CR BECOMES YFS29R.
- 2 YFS-CP & YFS-CPL LIMITER LINKS BRAZED TO MAKE OIL TIGHT SEAL.
3. THIS DRAWING TO BE INTERPRETED PER ASME Y14.5M-2009.
4. MAXIMUM VOLTAGE RATING: 250 VOLTS.
- 5 CRIMP AREA.
- 6 CATALOG NUMBER "PT6515" ADAPTOR IS REQUIRED TO USE "U" TYPE DIES IN THE Y45 SERIES TOOLS.
- 7 CATALOG NUMBER "PUADP-1" ADAPTOR IS REQUIRED TO USE "U" TYPE DIES IN THE Y46 SERIES TOOLS.
- 8 Y35P3 INDENTOR ADAPTOR IS REQUIRED FOR Y34PR INDENTOR.



REFERENCES:
SD..027894-01 YFS39CR YFS44CR
SD..027898-01 YFS39CPL, YFS44CPL
SC..007802-01 YFS4CCR

TO ORDER BURNDY® PRODUCTS CALL				LIMITER ASSEMBLY			
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com				ITEM NO: --			
				CAT. NO: YFS (GEN'L)			
				DRAWN BY: R.M.W	12/2/1941		
				CHECKER: WK	12/7/1941		
				DSN APRVL: --			
				MFG APRVL: --			
				QA APRVL: --			
				MKT APRVL: --			
				PROD FAM: --		DRAWING NO	
				PROJECT #: --		SD009354-01	
				DOCUMENT TYPE: SALES		SHEET 1 OF 1	
				REL LEVEL: Released			
					SIZE D		
						B	