




I.P.S. PIPE ACCOMMODATED			WIRE RANGE	
NOMINAL SIZE	ACTUAL OUTER DIAMETER		AWG	METRIC WIRE SIZE
	(IN)	(mm)		
2 1/2	2.875	[73]	6 STR (.184) - 250kcmil (.575)	16mm ² STR [5.1] 120mm ² STR [14.4]
3	3.500	[89]		
3 1/2	4.000	[102]		
4	4.500	[114]		

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	06/26/2020	REDRAWN IN INVENTOR AND CONDUCTOR HOLE CHAMFER REMOVED	53781	PB	RG



NOTES:

1. MATERIAL: ALUMINUM (3/8 - 16 UNC SCREWS ARE STEEL).
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
3. UL467 LISTED, FILE NO. E9999.
4. PENETROX™ OXIDE INHIBITING JOINT COMPOUNDS ARE RECOMMENDED. FOR ALL ALUMINUM APPLICATIONS.
5. RECOMMENDED TORQUE: 240 LBin [27.0 Nm].

TO ORDER BURNDY® PRODUCTS CALL				GROUND CLAMP			
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)				ITEM NO: 262004			
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)				CAT. NO: GC22A			
FOR PRODUCT INFO: http://www.burndy.com				DRAWN BY: D.BOISVERT 04/15/1999			
				CHECKER: J.MICHAUD 04/19/1999			
				DSN APRVL: G.DITROIA 05/25/1999			
				MFG APRVL: --			
				QA APRVL: J.BRODEUR 05/26/1999			
				MKT APRVL: P.MITCHELL 05/24/1999			
				PROD FAM: --			
				PROJECT #: --			
				DOCUMENT TYPE: SALES			
				REL LEVEL: Released			
				SIZE B			
				DRAWING NO SC212059-01			
				SHEET 1 OF 1			
				REV B			