



SC211202

COPPER CONDUCTOR ACCOMMODATED		CAT. NO.	H	J DIA.	L	W	T	TORQUE	
AWG	METRIC WIRE SIZE							Lb*in	N*m
4 SOL (.204 DIA) - 2/0 STR (.418 DIA)	[25mm <sup>2</sup> STR (6.48) - 70mm <sup>2</sup> STR (10.9)]	GB260SB	1.74 [44]	3/8-16	1.06 [27]	1.52 [39]	1/4"	240	27.0

REV.	DATE	DESCRIPTION	BY	C'K'D.
0	8/16/97	DRAWING RELEASED	PL	KH
1	3/13/98	ADDED NOTE 4 PER E9999.	BM	KRB



NOTES:

1. MATERIAL: CAST COPPER ALLOY.
2. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
3. FOR BAR THICKNESS FROM 1/4" TO 1/2" ADD THE SUFFIX "-T4" TO THE CATALOG NUMBER. FOR BAR THICKNESS FROM 1/2" TO 1" ADD THE SUFFIX "-T8" TO THE CATALOG NUMBER. "H" DIM ONLY APPLIES TO THE STANDARD (NON-SUFFIX) CATALOG NUMBERS SHOWN IN TABLE ABOVE.
4. UL 467 LISTED, SUITABLE FOR DIRECT BURIAL, FILE E9999.

**GROUND CONNECTOR**

CAT NO: <b>GB260SB</b>	SCALE: NTS
DRAWN: P. LAPONTUS	8/16/97
CHECKED: K. HENRY	9/24/97
DESIGN APPL: K. MELLO	9/17/97
WKS APPL: N/A	
S.A. APPL: S. GRAY	9/24/97
PKTS APPL: P. WERTHMAN	9/23/97
EQD FILE: SC211202-01-1	PH. REF: N/A
	IND. REF: N/A
PROJECT: D. O. 59884	
DRAWING NO. <b>SC211202</b>	
REV. <b>1</b>	
SHEET 1 OF 1	

**BURNDY**

REV. 061995