



REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
F	05/06/2013	CHANGED L REF DIMENSION TO L	31563	AB	BT

CATALOG NUMBER	COPPER CONDUCTOR			DIMENSIONS				
	SIZE	METRIC SIZE	STR.	B MIN.	C	L	O.D.	T REF.
YGA8C2N	#8 STR (.146 DIA.)	[10mm ² (.165mm DIA.)]	7	.78 [20]	.83 [21]	4.09 [104]	.27 [7]	.12 [3]
YGA6C2N	#6 STR (.184 DIA.)	----	7	1.09 [28]	.83 [21]	4.40 [112]	.29 [7]	.12 [3]
YGA4C2N	#4 STR (.232 DIA.)	----	7	1.09 [28]	.83 [21]	4.45 [113]	.34 [9]	.12 [3]
YGA2C2N	#2 STR (.292 DIA.)	----	7	1.22 [31]	.83 [21]	4.64 [118]	.42 [11]	.12 [3]
YGA252N	1/0 (.372 DIA.)	----	7, 19	1.35 [34]	.83 [21]	4.81 [122]	.51 [13]	.12 [3]
YGA262N	2/0 (.420 DIA.)	[70mm ² (10.9mm DIA.)]	7, 19, 37	1.45 [37]	.83 [21]	4.97 [126]	.56 [14]	.12 [3]
YGA282N	4/0 (.528 DIA.)	----	7, 12, 19	1.57 [40]	1.00 [25]	5.17 [131]	.69 [18]	.14 [4]
YGA292N	250 kcmil (.575 DIA.)	[120mm ² (14.4mm DIA.)]	7, 19, 37	1.57 [40]	1.09 [28]	5.21 [132]	.75 [19]	.16 [4]
YGA342N	500 kcmil (.813 DIA.)	[240mm ² (20.4mm DIA.)]	19, 37	2.20 [56]	1.52 [39]	6.08 [154]	1.06 [27]	.23 [6]

CATALOG NO.	TOLERANCE	
	C	L
YGA8C2N THRU YGA2C2N	±.03 [±1]	±.09 [±2]
YGA252N THRU YGA342N	±.08 [±2]	±.12 [±3]

NOTES:

- MATERIAL: COPPER
- BARREL IS PREFILLED WITH PENETROX™ "E" AND INDIVIDUALLY SEALED.
- WHERE A "U" OR "PU" IS RECOMMENDED WITH THE Y45 HYPRESS™, A PT6515 ADAPTER MUST BE USED.
- WHERE A "U" OR "PU" IS RECOMMENDED WITH THE Y46 HYPRESS™, A PUADP-1 ADAPTER MUST BE USED.
- ALL CONNECTORS ARE UL LISTED TO UL467 EXCEPT THE YGA4C-2N IS NOT UL LISTED.
- UL & CSA CERTIFIED PRODUCTS ARE SUITABLE FOR DIRECT BURIAL IN EARTH OR CONCRETE.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED.
- Y35P3 INDENTOR ADAPTOR REQUIRED FOR YA34PR INDENTOR.
- PERMANENT DIE IN TOOLING.
- FOR USE BY CUSTOMERS THAT HAVE THIS HYPRESS™, NO NEW Y34PA HYPRESS™ TOOLS ARE BEING PROCESSED. Y34PA USES A--D NEST DIES ONLY.
- "X", "W-RT", "U", & "L" DIE SETS ARE COLOR CODED. "A", "B", AND "C" DIES ARE NOT COLOR CODED.
- YGA8C-2N, YGA6C-2N, & YGA4C-2N ARE NOT CSA CERTIFIED. ALL OTHERS ARE CSA CERTIFIED.



TO ORDER BURNDY® PRODUCTS CALL		HYLUG™ COPPER GROUND	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: N/A	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: YGA--2N (TABLE)	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: P LAPONIUS 1/20/1997	
		CHECKER: J MICHAUD 1/21/1997	
		DSN APRVL: K MELLO 5/10/1996	
		MFG APRVL: --	
		QA APRVL: J BRODEUR 9/27/1996	
		MKT APRVL: T NELSON 9/24/1996	
		PROD FAM: --	
		DRAWING NO	
		SD082469	
		REV	
		F	
		SHEET 1 OF 2	

INSTALLATION TOOLING (# CRIMPS)

CATALOG NO.	COLOR CODE	DIE INFORMATION		MECHANICAL					HYDRAULIC					DIELESS (# CRIMPS)	WIRE STRIP LENGTH	
		DIE INDEX	TYPE	Y2MR	OUR840	MD6 MD7	MD6--R2 BAT500	MD7-34R	Y34A Y34B Y34BH	Y35, Y39 Y750, BAT35 BAT750, PAT750	Y46 PAT46	Y45	Y48B			Y60BHU
YGA8C2N	RED	49	RED DIE SET	RED (2)	X8CRT (2)	W 8CVT (2) W 8CRT (2)	W 8CVT (2) W 8CRT (2)	W 8CVT (2) W 8CRT (2)	----	U 8CRT (2)	U 8CRT (2)	U 8CRT (2)	----	----	RATCHET: Y8MRB-1 (2) MECHANICAL: MY29-3 (2) MY29-11 (2)	7/8"
			NEST	----	----	----	----	----	----	----	----	----	----	----		
			INDENTOR	----	----	----	----	----	----	----	----	----	----	----		
YGA6C2N	BLUE	7 374	BLUE DIE SET	BLUE (2)	X5CRT (2)	W 5CRT (2) W 5CVT (2)	W 5CRT (2) W 5CVT (2)	W 5CRT (2) W 5CVT (2)	----	U 5CRT (2) U 8CABT (2)	U 5CRT (2) U 8CABT (2)	U 5CRT (2) U 8CABT (2)	----	----	MECHANICAL: MY29-3 (2) MY29-11 (2) HYDRAULIC: Y644M (1) BAT644M (1) PAT81K- Y81K- SERIES (2)	1-3/16"
			NEST	----	----	----	----	B6CD (1) A6CD (1)	U 6CD-1 (1)	U 6CD-1 (1)	U 6CD-1 (1)	----	----			
			INDENTOR	----	----	----	----	Y34PR	Y34PR	Y34PR	Y34PR	----	----			
YGA4C2N	GRAY	8 346	GRAY DIE SET	GRAY (4)	X4CRT (2)	W 4CRT (2) W 4CVT (2)	W 4CRT (2) W 4CVT (2)	W 4CRT (2) W 4CVT (2)	----	U 4CRT (2) U 6CABT (2)	U 4CRT (2) U 6CABT (2)	U 4CRT (2) U 6CABT (2)	----	----	PAT81K- Y81K- SERIES (2)	1-3/16"
			NEST	----	----	----	----	B2CD (1) A2CD (1)	U 2CD-1 (1)	U 2CD-1 (1)	U 2CD-1 (1)	----	----			
			INDENTOR	----	----	----	----	Y34PR	Y34PR	Y34PR	Y34PR	----	----			
YGA2C2N	BROWN	10	BROWN DIE SET	BROWN (4)	X2CRT (2)	W 2CRT (2) W 2CVT (2)	W 2CRT (2) W 2CVT (2)	W 2CRT (2) W 2CVT (2)	----	U 2CRT (2)	U 2CRT (2)	U 2CRT (2)	----	----	↑	1-5/16"
			NEST	----	----	----	----	B2CD (1) A2CD (1)	U 2CD-1 (1)	U 2CD-1 (1)	U 2CD-1 (1)	----	----			
			INDENTOR	----	----	----	----	Y34PR	Y34PR	Y34PR	Y34PR	----	----			
YGA252N	PINK	12 348	PINK DIE SET	----	X25RT (4)	W 25RT (4) W 25VT (4)	W 25RT (4) W 25VT (4)	W 25RT (4) W 25VT (4)	A 25R (2)	U 25RT (2) U 2CABT (2)	U 25RT (2) U 2CABT (2)	U 25RT (2) U 2CABT (2)	----	----	↑	1-7/16"
			NEST	----	----	----	----	B25D (1) A25D (1)	U 25D-1 (1)	U 25D-1 (1)	U 25D-1 (1)	----	----			
			INDENTOR	----	----	----	----	Y34PR	Y34PR	Y34PR	Y34PR	----	----			
YGA262N	BLACK	13	BLACK DIE SET	----	X26RT (4)	W 26RT (4) W 26VT (4)	W 26RT (4) W 26VT (4)	W 26RT (4) W 26VT (4)	----	U 26RT (2)	U 26RT (2)	U 26RT (2)	----	----	↑	1-9/16"
			NEST	----	----	----	----	B26D (1) A26D (1)	U 26D-1 (1)	U 26D-1 (1)	U 26D-1 (1)	----	----			
			INDENTOR	----	----	----	----	Y34PR	Y34PR	Y34PR	Y34PR	----	----			
YGA282N	PURPLE	15	PURPLE DIE SET	----	X28RT (4)	W 28RT (4) W 28VT (4)	W 28RT (4) W 28VT (4)	W 28RT (4) W 28VT (4)	----	U 28RT (2)	U 28RT (2)	U 28RT (2)	C28R (2)	L28RT (1)	MECHANICAL: MY29-3 (2) MY29-11 (2) HYDRAULIC: Y644M (1) BAT644M (1) PAT81K- Y81K- SERIES (2)	1-11/16"
			NEST	----	----	----	----	B28D (1) A28D (1)	U 28D-1 (1)	U 28D-1 (1)	U 28D-1 (1)	C28D (1)	----			
			INDENTOR	----	----	----	----	Y34PR	Y34PR	Y34PR	Y34PR	Y48PR	----			
YGA292N	YELLOW	16	YELLOW DIE SET	----	X29RT (4)	W 29VT (4) W 29VT (4)	W 29RT (4) W 29VT (4)	W 29VT (4)	A 29R (2)	U 29RT (2)	U 29RT (2)	U 29RT (2)	C29R (2)	L29RT (1)	↑	1-11/16"
			NEST	----	----	----	----	B29D (2) A29D (2)	U 29D-1 (2)	U 29D-1 (2)	U 29D-1 (2)	C29D (1)	----			
			INDENTOR	----	----	----	----	Y34PR	Y34PR	Y34PR	Y34PR	Y48PR	----			
YGA342N	BROWN	20 299	BROWN DIE SET	----	----	----	W 34RT (4) W 34VT (4)	W 34VT (4)	----	U 34RT (4) U 31ART (4)	U 34RT (4) P34RT (4) U 31ART (4)	U 34RT (4) U 31ART (4)	C34R (2) C31AR (2)	L34RT (2)	HYDRAULIC: Y644M (1) BAT644M (1) PAT81K- Y81K- SERIES (2)	2-5/16"
			NEST	----	----	----	----	----	B34D (2) A34D (2)	U 34D-1 (2)	U 34D-1 (2)	U 34D-1 (2)	C34D (2)	----		
			INDENTOR	----	----	----	----	----	Y34PR	Y34PR	Y34PR	Y34PR	Y48PR	----		

SEE SHEET #1 FOR NOTES

TO ORDER BURNDY® PRODUCTS CALL		HYLUG™ COPPER GROUND	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: N/A	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: YGA--2N (TABLE)	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: P LAPONILUS 1/20/1997	
		CHECKER: J MICHAUD 1/21/1997	
		DSN APRVL: K MELLO 3/10/1996	
		MKT APRVL: T NELSON 9/24/1996	
		QA APRVL: J BRODEUR 9/27/1996	
		PROJ FAM: --	
		PROJECT #: --	
		DOCUMENT TYPE: SALES	
		REL LEVEL: Released	
		SIZE: D	
		DRAWING NO: SD082469	
		REV: F	
		SHEET 2 OF 2	