



DRAWING NO. SE208074		7		6		5		4		3		2		1					
CATALOG NUMBER	ACCOMMODATES	STUD SIZE	DIMENSIONS											CABLE STRIP LENGTH	INSTALLATION TOOLING				
	FLEXIBLE CABLE CODE AWG		B	C	C TOL.	E 	K DIA.	L	N 	T	Z  MIN.	BELL	O.D.		DIELESS TOOLS		 Y35, Y39, Y750, PAT750,Y46,PAT46		
															MECHANICAL HYTOOL™(CRIMPS)	HYDRAULIC HYPRESS™	DIE INDEX	COLOR CODE	DIE NUMBER (# OF CRIMPS)
YAV4C2TC14FXB	#4 CLASS B,C,G,H,I,K,M DLO (105/24)	1/4	1.22 [31]	.55 [14]	±.03 [±1]	.62 [16]	.27 [7]	2.81 [71]	.31 [8]	.09 [2]	.33 [8]	.44 [11]	.38 [10]	1-5/16" [33]	MY293 (2) MY2911 (2) YIMRTC(4) Y122CMR (4)	Y81KFT(1) PAT81KFT(1)	8	GRAY	U4CRT (2 CRIMPS)
YAV4C2TC14E2FXB		1/4	1.22 [31]	.55 [14]	±.03 [±1]	.75 [19]	.27 [7]	2.93 [74]	.31 [8]	.09 [2]	.33 [8]	.44 [11]	.38 [10]	1-5/16" [33]					
YAV4C2TC14E1FXB		1/4	1.22 [31]	.55 [14]	±.03 [±1]	1.00 [25]	.27 [7]	3.18 [81]	.31 [8]	.09 [2]	.33 [8]	.44 [11]	.38 [10]	1-5/16" [33]					
YAV4C2TC516FXB		5/16	1.22 [31]	.55 [14]	±.03 [±1]	1.00 [25]	.33 [8]	3.24 [82]	.34 [9]	.09 [2]	.36 [9]	.44 [11]	.38 [10]	1-5/16" [33]					
YAV4C2TC38FXB		3/8	1.22 [31]	.58 [15]	±.04 [±1]	1.00 [25]	.41 [10]	3.37 [86]	.41 [10]	.09 [2]	.42 [11]	.44 [11]	.38 [10]	1-5/16" [33]					
YAV4C2NFXB		1/2	1.22 [31]	.83 [21]	±.04 [±1]	1.75 [44]	.56 [14]	4.56 [116]	.62 [16]	.12 [3]	.64 [16]	.44 [11]	.38 [10]	1-5/16" [33]					
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---
YAV3C2TC516FXB	#3 CLASS B,C,G,H,I,K,M DLO (125/24)	5/16	1.48 [38]	.60 [15]	±.03 [1]	1.00 [25]	.33 [8]	3.51 [89]	.34 [9]	.09 [2]	.36 [9]	.49 [12]	.42 [11]	1-9/16 [40]	MY293 (2) MY2911 (2) YIMRTC(4) Y122CMR (4)	Y81KFT(1) PAT81KFT(1)	9	WHITE	U3CRT (2 CRIMPS)
YAV3C2TC38FXB		3/8	1.48 [38]	.60 [15]	±.04 [1]	1.00 [25]	.41 [10]	3.64 [92]	.41 [10]	.09 [2]	.42 [11]	.49 [12]	.42 [11]	1-9/16 [40]					
YAV3C2NFXB		1/2	1.48 [38]	.83 [21]	±.04 [1]	1.75 [44]	.56 [14]	4.83 [123]	.62 [16]	.12 [3]	.64 [16]	.49 [12]	.42 [11]	1-9/16 [40]					
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---
YAV2C2TC14FXB	#2 CLASS B,C,G,H,I,K,M DLO (150/24)	1/4	1.35 [34]	.68 [17]	±.03 [1]	.62 [16]	.27 [7]	3.00 [76]	.31 [8]	.10 [3]	.33 [8]	.54 [14]	.46 [12]	1-7/16 [37]	MY293 (2) MY2911 (2) YIMRTC(4) Y122CMR (4)	Y81KFT (1) PAT81KFT (1)	10	BROWN	U2CRT (2 CRIMPS)
YAV2C2TC14E2FXB		1/4	1.35 [34]	.68 [17]	±.03 [1]	.75 [19]	.27 [7]	3.13 [79]	.31 [8]	.10 [3]	.33 [8]	.54 [14]	.46 [12]	1-7/16 [37]					
YAV2C2TC14E1FXB		1/4	1.35 [34]	.68 [17]	±.03 [1]	1.00 [25]	.27 [7]	3.38 [86]	.31 [8]	.10 [3]	.33 [8]	.54 [14]	.46 [12]	1-7/16 [37]					
YAV2C2TC516FXB		5/16	1.35 [34]	.68 [17]	±.03 [1]	1.00 [25]	.33 [8]	3.44 [87]	.34 [9]	.10 [3]	.36 [9]	.54 [14]	.46 [12]	1-7/16 [37]					
YAV2C2TC38FXB		3/8	1.35 [34]	.68 [17]	±.03 [1]	1.00 [25]	.41 [10]	3.57 [91]	.41 [10]	.10 [3]	.42 [11]	.54 [14]	.46 [12]	1-7/16 [37]					
YAV2C2NT38FXB		3/8	1.35 [34]	.55 [14]	±.03 [1]	1.00 [25]	.41 [10]	3.57 [91]	.41 [10]	.10 [3]	.42 [11]	.54 [14]	.46 [12]	1-7/16 [37]					
YAV2C2NFXB		1/2	1.35 [34]	.83 [21]	±.04 [1]	1.75 [44]	.56 [14]	4.76 [121]	.62 [16]	.12 [3]	.64 [16]	.54 [14]	.46 [12]	1-7/16 [37]					
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	
YAV1C2TC14FXB	#1 CLASS B,C,G,H,I,K,M DLO (225/24)	1/4	1.50 [38]	.75 [19]	±.03 [1]	.62 [16]	.27 [7]	3.17 [81]	.31 [8]	.12 [3]	.33 [8]	.60 [15]	.51 [13]	1-9/16 [40]	MY293 (2) MY2911 (2) YIMRTC(4)	Y81KFT (1) PAT81KFT (1)	11	GREEN	U1CRT-1 (2 CRIMPS)
YAV1C2TC14E2FXB		1/4	1.50 [38]	.75 [19]	±.03 [1]	.75 [19]	.27 [7]	3.30 [84]	.31 [8]	.12 [3]	.33 [8]	.60 [15]	.51 [13]	1-9/16 [40]					
YAV1C2TC38FXB		3/8	1.50 [38]	.75 [19]	±.03 [1]	1.00 [25]	.41 [10]	3.74 [95]	.41 [10]	.12 [3]	.42 [11]	.60 [15]	.51 [13]	1-9/16 [40]					
YAV1C2NFXB		1/2	1.50 [38]	.83 [21]	±.04 [1]	1.75 [44]	.56 [14]	4.92 [125]	.62 [16]	.11 [3]	.64 [16]	.60 [15]	.51 [13]	1-9/16 [40]					
NOTES:																			
1. MATERIAL: COPPER.																			
2. FINISH: TIN PLATED. "FOR ALTERNATIVE FINISH ADD ONE OF THE FOLLOWING SUFFIXES: NICKEL = NK, LEAD = LD, BARE = BR, SILVER = SV"																			
 CATALOG NUMBER "PUADP-1" ADAPTOR IS REQUIRED TO USE "U" TYPE DIES IN THE Y46 SERIES TOOLS.																			
4. REFERENCE THE BURNDY® MASTER CATALOG "INSTALLATION TOOL INDEX" FOR ADDITIONAL TOOLING.																			
5. BELLED BARREL ENDS PROVIDE EASY CABLE INSERTION AND STRAIN RELIEF.																			
6. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.																			
 FOR UNDRILLED VERSIONS AND SUFFIX "U" TO END OF CATALOG NUMBER. FOR UNDRILLED VERSIONS,USE D MIN = N MAX + E MAX + Z MIN.																			
 CONNECTORS ARE UL LISTED; UNDRILLED VERSIONS ARE NOT UL LISTED.																			
 CONNECTORS ARE CSA CERTIFIED; UNDRILLED VERSIONS ARE NOT CSA CERTIFIED.																			
SEE SHEET ONE FOR VIEWS																			
TO ORDER BURNDY® PRODUCTS CALL  UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)  CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)  FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>															TELECOM BELLED HYLUG™				
															ITEM NO: N/A				
															CAT. NO: YA-2-FXB- (TABLE)				
															DRAWN BY: J.GAUDET 11/04/92				
															CHECKER: K.HENRY 11/18/92				
															DSN APPVL: C.PALAGI 11/20/92				
															MFG APPVL: N/A --				
															QA APPVL: A.LLOYD 11/21/92				
															MKT APPVL: L.HERRON 11/23/92				
															PROD FAM: --				
															PROJECT #: FPN1512073				
															SIZE				
															DOCUMENT TYPE: Sales				
															REL LEVEL: Released				
															D				
															SHEET 2 OF 6				
															M				
REV: PE0200		8		7		6		5		4		3		2		1			



DRAWING NO. SE208074		7		6		5		4		3		2		1											
												REV	DATE		DESCRIPTION		ECO	BY	C.H.K.						
												M	2019-10-11 00:00:00 EDT		UPDATED AS PER MARKUP		52318	YR	SS						
CATALOG NUMBER	ACCOMMODATES	STUD SIZE	DIMENSIONS											CABLE STRIP LENGTH	INSTALLATION TOOLING										
	FLEXIBLE CABLE CODE AWG														DIELESS TOOLS		3 Y35, Y39, Y750, Y46								
			B	C	C TOL.	E	K DIA.	L	N	T	Z MIN.	BELL	O.D.		MECHANICAL HYTOOL	HYDRAULIC TM HYPRESS	DIE INDEX	COLOR CODE	DIE NUMBER (# OF CRIMPS)						
"CONNECTORS BELOW ARE FOR FLEXIBLE CONDUCTOR ONLY"																									
YA302TC38FXB	250 Kcmil FLEX CLASS G 259 STR. CLASS H 427 STR.	3/8	2.16 [55]	1.20 [30]	±.04 [1]	1.00 [25]	.40 [10]	4.61 [117]	.41 [10]	.16 [4]	.42 [11]	.95 [24]	.81 [21]	2-1/4 [57]	---	Y81KFT (2) PAT81KFT (2)	16	YELLOW	U29RT (2 CRIMPS)						
YA302NFXB		1/2	2.16 [55]	1.20 [30]	±.04 [1]	1.75 [44]	.56 [14]	5.80 [147]	.62 [16]	.16 [4]	.64 [16]	.95 [24]	.81 [21]	2-1/4 [57]	---	Y644 (1) PAT644(1) PAT444(1)									
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---						
YA312TC38FXB	263 Kcmil (650/24) 250 FLEX CLASS I, K, M	3/8	2.18 [55]	1.29 [33]	±.04 [1]	1.00 [25]	.40 [10]	4.66 [118]	.41 [10]	.18 [5]	.42 [11]	1.03 [26]	.88 [22]	2-1/4 [57]	---	Y81KFT (2) PAT81KFT (2)	17	WHITE	U30RT (4 CRIMPS)						
YA312NTC38FXB		3/8	2.18 [55]	1.29 [33]	±.04 [1]	1.75 [44]	.40 [10]	5.41 [137]	.41 [10]	.18 [5]	.42 [11]	1.03 [26]	.88 [22]	2-1/4 [57]	---	Y644 (1) PAT644(1) PAT444(1)									
YA312NFXB		1/2	2.18 [55]	1.29 [33]	±.04 [1]	1.75 [44]	.56 [14]	5.85 [149]	.62 [16]	.18 [5]	.64 [16]	1.03 [26]	.88 [22]	2-1/4 [57]	---	---									
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---						
YA322TC38FXB	300 kcmil FLEX CLASS G,H,I,K,M 313 DLO(775/24)	3/8	2.32 [60]	1.40 [36]	±.04 [1]	1.00 [25]	.40 [10]	4.85 [123]	.41 [10]	.19 [5]	.42 [11]	1.12 [28]	.95 [24]	2-1/4 [57]	---	Y81KFT (2) PAT81KFT (2)	18	RED	U31RT (4 CRIMPS)						
YA322NTC38FXB		3/8	2.32 [60]	1.40 [36]	±.04 [1]	1.75 [44]	.40 [10]	5.60 [142]	.41 [10]	.19 [5]	.42 [11]	1.12 [28]	.95 [24]	2-1/4 [57]	---	Y644 (1) PAT644(1) PAT444(1)									
YA322NFXB		1/2	2.32 [60]	1.40 [36]	±.04 [1]	1.75 [44]	.56 [14]	6.04 [153]	.62 [16]	.19 [5]	.64 [16]	1.12 [28]	.95 [24]	2-1/4 [57]	---	---									
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---						
YA342TC14E2FXB	350 kcmil FLEX CLASS G,H,I,K,M 373 DLO(925/24)	1/4	2.48 [63]	1.55 [39]	±.04 [1]	.75 [19]	.27 [7]	4.66 [118]	.31 [8]	.23 [6]	.33 [8]	1.24 [31]	1.06 [27]	2-9/16 [65]	---	Y81KFT (2) PAT81KFT (2)	19	BLUE	U32RT (4 CRIMPS)						
YA342TC38FXB		3/8	2.48 [63]	1.55 [39]	±.04 [1]	1.00 [25]	.40 [10]	5.10 [130]	.41 [10]	.23 [6]	.42 [11]	1.24 [31]	1.06 [27]	2-9/16 [65]	---	Y644 (1) PAT644(1) PAT444(1)									
YA342NFXB		1/2	2.48 [63]	1.55 [39]	±.04 [1]	1.75 [44]	.56 [14]	6.29 [160]	.62 [16]	.23 [6]	.64 [16]	1.24 [31]	1.06 [27]	2-9/16 [65]	---	---									
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---						
YA362TC38FXB	500 kcmil FLEX CLASS G,H 444 DLO(1100/24)	3/8	2.95 [75]	1.73 [44]	±.06 [2]	1.00 [25]	.40 [10]	5.84 [148]	.50 [13]	.26 [7]	.52 [13]	1.40 [36]	1.18 [30]	3-1/16 [78]	---	Y81KFT (2) PAT81KFT (2)	20	BROWN	U34RT (4 CRIMPS)						
YA362NFXB		1/2	2.95 [75]	1.73 [44]	±.06 [2]	1.75 [44]	.56 [14]	6.84 [174]	.62 [16]	.26 [7]	.64 [16]	1.40 [36]	1.18 [30]	3-1/16 [78]	---	Y644 (1) PAT644(1) PAT444(1)									
NOTES:																									
1. MATERIAL: COPPER.																									
2. FINISH: TIN PLATED. "FOR ALTERNATIVE FINISH ADD ONE OF THE FOLLOWING SUFFIXES: NICKEL = NK, LEAD = LD, BARE = BR, SILVER = SV"																									
3 CONNECTORS ARE UL LISTED; UNDRILLED VERSIONS ARE NOT UL LISTED.																									
3 CONNECTORS ARE CSA CERTIFIED; UNDRILLED VERSIONS ARE NOT CSA CERTIFIED.																									
SEE SHEET 1 FOR VIEWS AND TOLERANCES																									
3 CATALOG NUMBER "PUADP-1" ADAPTOR IS REQUIRED TO USE "U" TYPE DIES IN THE Y46 SERIES TOOLS.																									
4. REFERENCE THE BURNDY® PRODUCTS MASTER CATALOG "INSTALLATION TOOL INDEX" FOR ADDITIONAL TOOLING.																									
5. BELLED BARREL ENDS PROVIDE EASY CABLE INSERTION AND STRAIN RELIEF.																									
6. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.																									
7 FOR UNDRILLED VERSIONS AND SUFFIX "U" TO END OF CATALOG NUMBER. FOR UNDRILLED VERSIONS,USE D MIN = N MAX + E MAX + Z MIN.																									
TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>												TELECOM BELLED HYLUG™ ITEM NO: N/A CAT. NO: YA-2-FXB- (TABLE) DRAWN BY: M.PITTENDREIGH 8/02/93 CHECKER: R.ROBICHEAU 8/10/93 DSN APPVL: C.PALAGI 8/11/93 MFG APPVL: N/A -- QA APPVL: A.LLOYD 8/31/93 MKT APPVL: M.BLAKE 8/26/93 PROD FAM: -- PROJECT #: -- DOCUMENT TYPE: Sales REL LEVEL: Released							SCALE: NTS DRAWING NO REV SE208074 M						
8												7		6		5		4		3		2		1	

REV: PE0200

**A**

DRAWING NO. SE208074		7		6		5		4		3		2		1						
CATALOG NUMBER	ACCOMMODATES	STUD SIZE	DIMENSIONS												CABLE STRIP LENGTH	INSTALLATION TOOLING				
	FLEXIBLE CABLE CODE AWG		B	C	C TOL.	E	K DIA.	L	N	T	Z MIN.	BELL	O.D.	DIELESS TOOLS		Y35, Y39, Y750, Y46				
														MECHANICAL HYTOOL™(CRIMPS)		HYDRAULIC HYPRESS™	DIE INDEX	COLOR CODE	DIE NUMBER (# OF CRIMPS)	
"CONNECTORS BELOW ARE FOR FLEXIBLE CONDUCTOR ONLY"																				
YA382TC38FXB	500 kcmil FLEX CLASS H,I,K 550 kcmil FLEX CLASS G,H,I 535 DLO(1350/24)	3/8	3.08 [78]	1.84 [47]	±.06 [2]	1.00 [25]	.40 [10]	6.01 [153]	.50 [13]	.26 [7]	.53 [13]	1.47 [37]	1.25 [32]	3-3/16 [81]	---	Y81KFT (2) PAT81KFT (2) Y644 (1) PAT644(1) PAT444(1)	L99	PINK	U38XRT (4 CRIMPS)	
YA382NFXB		1/2	3.08 [78]	1.84 [47]	±.06 [2]	1.75 [4]	.56 [14]	7.01 [178]	.62 [16]	.26 [7]	.64 [16]	1.47 [37]	1.25 [32]	3-3/16 [81]						
YA382FXBG2		3/8	3.08 [78]	1.84 [47]	±.06 [2]	2.00 [51]	.40 [10]	6.82 [173]	.41 [10]	.27 [7]	.42 [11]	1.47 [37]	1.25 [32]	3-3/16 [81]						
YA382FXBG3		1/2	3.08 [78]	1.84 [47]	±.06 [2]	1.19 [30]	.52 [13]	6.26 [159]	.53 [13]	.27 [7]	.55 [14]	1.47 [37]	1.25 [32]	3-3/16 [81]						
----	----	----	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	
YA402NFXB	650 kcmil FLEX CLASS G 646 DLO(1600/24)	1/2	3.24 [82]	1.98 [50]	±.06 [2]	1.75 [44]	.56 [14]	7.22 [183]	.62 [16]	.30 [8]	.64 [16]	1.58 [40]	1.35 [34]	3-5/16 [84]	---	Y81KFT (3) PAT81KFT (3) Y644 (1) PAT644(1) PAT444(1)	24	BLACK	U39RT (4 CRIMPS)	
----	----	----	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	
YA442TC38FXB	750 kcmil FLEX CLASS G,H,I 777 DLO(12925/24)	3/8	3.33 [85]	2.19 [56]	±.06 [2]	1.00 [25]	.40 [10]	6.44 [163]	.50 [13]	.33 [8]	.42 [11]	1.76 [45]	1.50 [38]	3-7/16 [87]	---	Y81KFT (3) PAT81KFT (3) Y644 (1) PAT644(1) PAT444(1)	L115	YELLOW	U44XRT (4 CRIMPS)	
YA442TC58E16FXB		5/8	3.33 [85]	2.19 [56]	±.06 [2]	1.75 [44]	.68 [17]	7.44 [189]	.62 [16]	.33 [8]	.64 [16]	1.76 [45]	1.50 [38]	3-7/16 [87]						
YA442NFXB		1/2	3.33 [85]	2.19 [56]	±.06 [2]	1.75 [44]	.56 [14]	7.44 [189]	.62 [16]	.33 [8]	.64 [16]	1.76 [45]	1.50 [38]	3-7/16 [87]						
----	----	----	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	
YA462NFXB	1111 Kcmil (2750/24)	1/2	3.58 [91]	2.69 [68]	±.06 [2]	1.75 [44]	.56 [14]	7.91 [201]	.62 [16]	.39 [10]	.64 [16]	2.16 [55]	1.84 [47]	3-11/16 [94]	---	---	29	YELLOW	P45RT (6 CRIMPS)	
YA462NFXBUNPL		1/2	3.58 [91]	2.69 [68]	±.06 [2]	1.75 [44]	.56 [14]	7.91 [201]	.62 [16]	.39 [10]	.64 [16]	2.16 [55]	1.84 [47]	3-11/16 [94]						
YA462NFXBDTS		1/2	3.58 [91]	2.69 [68]	±.06 [2]	1.75 [44]	.56 [14]	7.91 [201]	.62 [16]	.39 [10]	.64 [16]	2.16 [55]	1.84 [47]	3-11/16 [94]						
YA462TC38FXB		3/8	3.58 [91]	2.69 [68]	±.06 [2]	1.00 [25]	.41 [10]	6.91 [176]	.50 [13]	.39 [10]	.52 [13]	2.16 [55]	1.84 [47]	3-11/16 [94]						
YA462NNTFXB		1/2	3.58 [91]	2.06 [52]	±.06 [2]	1.75 [44]	.56 [14]	7.91 [201]	.63 [16]	.39 [10]	.64 [16]	2.16 [55]	1.84 [47]	3-11/16 [94]						
YA482NFXB	1550 Kcmil, CLASS K	1/2	3.90 [99]	3.10 [79]	±.06 [2]	1.75 [44]	.56 [14]	8.42 [214]	.62 [16]	.46 [12]	.64 [16]	2.50 [64]	2.13 [54]	4-1/16 [103]	---	---	33	GRAY	L47RT Y60BH HYPRESS™ (2 CRIMPS)	
NOTES: 1. MATERIAL: COPPER 2. FINISH:TIN PLATED. FOR UNPLATED PARTS USE SUFFIX "UNPL" ( EXAMPLE: YA26LTC12FXUNPL). FOR UNPLATED PARTS WITH INK MARKED BARREL USE SUFFIX "BR" (EXAMPLE: YAV6CLTC38FXBR). "FOR ALTERNATIVE FINISH ADD ONE OF THE FOLLOWING SUFFIXES: NICKEL = NK, LEAD = LD, BARE = BR, SILVER = SV" 3. CATALOG NUMBER "PUADP-1" ADAPTOR IS REQUIRED TO USE "U" TYPE DIES IN THE Y46 SERIES TOOLS. 4. REFERENCE THE BURNDY® PRODUCTS MASTER CATALOG "INSTALLATION TOOL INDEX" FOR ADDITIONAL TOOLING. 5. BELLED BARREL ENDS PROVIDE EASY CABLE INSERTION AND STRAIN RELIEF. 6. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY. 7. FOR UNDRILLED VERSIONS AND SUFFIX "U" TO END OF CATALOG NUMBER. FOR UNDRILLED VERSIONS,USE D MIN = N MAX + E MAX + Z MIN. 8. CONNECTORS ARE UL LISTED; UNDRILLED VERSIONS ARE NOT UL LISTED.																				
										9. CONNECTORS ARE CSA CERTIFIED; UNDRILLED VERSIONS ARE NOT CSA CERTIFIED. 10. DTS SUFFIX STANDS FOR OIL SEAL TIGHT BRAZING.										
										TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>										
										TELECOM BELLED HYLUG™ ITEM NO: N/A CAT. NO: YA-2-FXB- (TABLE) DRAWN BY: J. AYER 04/08/96 CHECKER: J. MICHAUD 04/09/96 DSN APPVL: C. PALAGI 01/24/96 MFG APPVL: - - - - QA APPVL: C.KOWALCZYK 11/07/2014 MKT APPVL: K.BOUTIN 11/05/2014 PROD FAM: - PROJECT #: - DOCUMENT TYPE: Sales REL LEVEL: Released										
										SCALE: NTS DRAWING NO REV SE208074 M SHEET 5 OF 6										
8		7		6		5		4		3		2		1						

