

DRAWING NO.  
**SD211939**

4

3

2

1

REV.	DATE	DESCRIPTION	ECO	BY	C.K'D.
C	11/12/13	UPDATED AS PER MARKUP	38075	VSK	MB

CATALOG NUMBER	ID EXPANDED		ID AFTER RECOVERY		WALL THICKNESS		CONDUCTOR RANGE	STANDARD REEL SIZE (FEET)
	IN.	mm	IN.	mm	IN.	mm		
HS_116T48PF	.062	1.6	.032	0.8	.018	0.45	#18	4
HS_116T300PF	.062	1.6	.032	0.8	.018	0.45	#18	25
HS_116T1200PF	.062	1.6	.032	0.8	.018	0.45	#18	100
HS_332T48PF	.094	2.4	.046	1.2	.020	0.51	#18-16	4
HS_332T300PF	.094	2.4	.046	1.2	.020	0.51	#18-16	25
HS_332T1200PF	.094	2.4	.046	1.2	.020	0.51	#18-16	100
HS_18T48PF	.125	3.2	.062	1.6	.020	0.51	#18-14	4
HS_18T300PF	.125	3.2	.062	1.6	.020	0.51	#18-14	25
HS_18T1200PF	.125	3.2	.062	1.6	.020	0.51	#18-14	100
HS_316T48PF	.187	4.8	.093	2.4	.020	0.51	#18-12	4
HS_316T300PF	.187	4.8	.093	2.4	.020	0.51	#18-12	25
HS_316T1200PF	.187	4.8	.093	2.4	.020	0.51	#18-12	100
HS_14T48PF	.250	6.4	.125	3.2	.025	0.64	#14-10	4
HS_14T300PF	.250	6.4	.125	3.2	.025	0.64	#14-10	25
HS_14T1200PF	.250	6.4	.125	3.2	.025	0.64	#14-10	100
HS_38T48PF	.375	9.5	.187	4.7	.025	0.64	#8-6	4
HS_38T300PF	.375	9.5	.187	4.7	.025	0.64	#8-6	25
HS_38T1200PF	.375	9.5	.187	4.7	.025	0.64	#8-6	100
HS_12T48PF	.500	12.7	.250	6.4	.025	0.64	#6-2	4
HS_12T300PF	.500	12.7	.250	6.4	.025	0.64	#6-2	25
HS_12T1200PF	.500	12.7	.250	6.4	.025	0.64	#6-2	100
HS_34T48PF	.750	19	.375	9.5	.030	0.76	#1-3/0	4
HS_34T300PF	.750	19	.375	9.5	.030	0.76	#1-3/0	25
HS_34T1200PF	.750	19	.375	9.5	.030	0.76	#1-3/0	100
HS_100T48PF	1.000	25.4	.500	12.7	.030	0.76	2/0-300	4
HS_100T300PF	1.000	25.4	.500	12.7	.030	0.76	2/0-300	25
HS_100T1200PF	1.000	25.4	.500	12.7	.030	0.76	2/0-300	100
HS_150T48PF	1.500	38.1	.750	19	.035	0.89	2/0-350	4
HS_150T1200PF	1.500	38.1	.750	19	.035	0.89	2/0-350	100
HS_200T48PF	2.000	50.8	1.000	25.7	.040	1.02	250-500	4
HS_200T1200PF	2.000	50.8	1.000	25.7	.040	1.02	250-500	100

**NOTES:**

- MATERIAL: THIN WALL POLYOLEFIN HEAT SHRINK TUBING.
- TO ORDER: EX:GHS 116T48PF

- B - BLACK  
BL - BLUE  
C - CLEAR  
G - GREEN  
R - RED  
W - WHITE  
Y - YELLOW

- ALL HEAT SHRINK TUBING MEETS UL224 AND CSA C22.2 NO. 198.1 (WITH THE EXCEPTION OF CLEAR HEAT SHRINK TUBING)
- CONTINUOUS OPERATING TEMPERATURE: -131°F (-55°C) TO 275°F (135°C)
- SHRINK TEMPERATURE: 284°F (120°C)
- 2:1 SHRINK RATIO.
- RATED VOLTAGE: 600V
- SHRINK INSTRUCTIONS:

- THE ARTICLE TO BE COVERED MUST BE CLEAN AND DRY.
- INSERT THE ARTICLE TO BE COVERED INTO TUBING.
- APPLY HEAT TO THE TUBING WITH A BACK AND FORTH MOTION FROM END TO END.
- REMOVE HEAT AS SOON AS THE TUBING BEGINS TO ASSUME THE SHAPE OF THE ARTICLE.

THIN WALL HEAT SHRINK

ITEM NO: ---


CAT NO: HS-T-PF (TABLE)

TO ORDER BURNDY® PRODUCTS CALL  
UNITED STATES:  
1-800-346-4175 (LONDONDERRY, NH)

CANADA:

1-800-361-6975 (QUEBEC)  
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

SCALE:	N/A	12/18/98	
DRAWN BY:	R. BOSSERT	1/07/99	
CHECKED:	P. LORONOUS	12/10/98	
DESIGNED:	D. WALTERS	---	
DATE:	---	---	
BY:	---	---	
QC APPRVE:	S. GRAY	12/15/98	DRAWING NO.
MKT APPRVE:	P. MITCHELL	12/11/98	SD211939
PROJECT #:	---	---	REV
DOCUMENT THE SIZES	---	---	---
REL LEVEL:	ALUCOUD	---	SHEET 1 of 1

4

3

2

1