


DRAWING NO.
SE088658-01

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
A	05/01/08	UPDATE NOTES PER M/U AND RE-ACTIVATE SALES DRAWING.	15535	RB	BV

CATALOG NUMBER	HOSE I.D.	L (LENGTH)
PT29900-6	3/16"	6'-0
PT29900-10		10'-0
PT29900-15		15'-0
PT29900-25	1/4"	25'-0
PT29901-10		10'-0
PT29901-15		15'-0
PT29901-25		25'-0



NOTES:

- 1 L (APPROX. OVERALL) IS EQUAL TO "L" (HOSE LENGTH) + 5.25".
- 2 DATE CODE ON HEX FITTING-TYP.-EA. END-
EXAMPLE: 9 4
 - ↑ LAST DIGIT OF YEAR
 - ↑ MONTH
- 3. THE HOSE ASSY IS SHIPPED FILLED WITH FC-BURNDY 'ALFLUID'.
- 4. IF HIGHEST REVISION OF THIS SALES PRINT IS AFFECTED UPDATE PRINT WSA208758 TO INCLUDE THE NEW REV.
- 5. FOR PROPER CARE AND MAINTENANCE, SEE HYDRAULIC HOSE CARE MANUAL.

HOSE CHARACTERISTICS:

- 1. NON-CONDUCTIVE HOSE.
- 2. MINIMUM BURST PRESSURE IS 40,000 PSI.
- 3. NOMINAL WORKING PRESSURE IS 10,000 PSI.
- 4. HOSE INSIDE DIA. IS 1/4" OR 3/16" - SEE TABLE.
- 5. MINIMUM BEND RADIUS: FOR 3/16" I.D. IS 4"
MINIMUM BEND RADIUS: FOR 1/4" I.D. IS 6".
- 6. OPERATING TEMPERATURE RANGE IS - 40°F TO 150°F.

SUPERSEDES: SD79214-6

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com		10,000 PSI HOSE ASSY	
ITEM NO: ---		CAT NO: PT29900- & PT29901 (SEE TABLE)	
SCALE: NTS	DRAWN BY: MV 09/17/84	BURNDY	DRAWING NO SE088658-01
CHECKER: MV 09/18/84	DSN APPVL: H. BANDS 07/18/84		
MFG APPVL: ---	QC APPVL: ---		
MKT APPVL: ---	PROD FAM: ---		
PROJECT #: ---	SIZE: D	SHEET 1 OF 1	
DOCUMENT TYPE: Sales	REL LEVEL: AutoCAD	REV A	