




CATALOG NUMBER	CONDUCTOR RANGE		DIMENSIONS		WIRE STRIP LENGTH		DIE NUMBER
	BARREL "A" CU. & ALUM.	BARREL "B" CU. & ALUM.	B MIN.	L	BARREL "A"	BARREL "B"	
YRB36U36TW	600 kcmil (.893 DIA.) 61 STR.	600 kcmil (.893 DIA.) 61 STR.	2.87 [73]	6.74 [171]	3"	3"	936
YRB39U28TW	750 kcmil (.988 DIA.) 61 STR.; 750 kcmil CMPCT (.908 DIA.) 61 STR.; 700 kcmil (.964 DIA.) 61 STR.	4/0 (.528 DIA.) 19 STR. OR 4/0 CMPCT (.475 DIA.) 19 STR.	2.87 [73]	6.74 [171]	3"	3"	936
YRB39U30TW	750 kcmil (.988 DIA.) 61 STR.; 750 kcmil CMPCT (.908 DIA.) 61 STR.; 700 kcmil (.964 DIA.) 61 STR.	300 kcmil (.630 DIA.) 37 STR.	2.87 [73]	6.74 [171]	3"	3"	936
YRB39U31TW	750 kcmil (.988 DIA.) 61 STR.; 750 kcmil CMPCT (.908 DIA.) 61 STR.; 700 kcmil (.964 DIA.) 61 STR.	350 kcmil (.681 DIA.) 37 STR. OR 350 kcmil CMPCT (.616 DIA.) 19 STR. ALUM.; 37 STR. ALUM. & CU.	2.87 [73]	6.74 [171]	3"	3"	936
YRB39U34TW	750 kcmil (.988 DIA.) 61 STR.; 750 kcmil CMPCT (.908 DIA.) 61 STR.; 700 kcmil (.964 DIA.) 61 STR.	500 kcmil (.813 DIA.) 37 STR. OR 500 kcmil CMPCT (.736 DIA.) 19 STR. ALUM.; 37 STR. ALUM. & CU.	2.87 [73]	6.74 [171]	3"	3"	936
YRB39U39TW	750 kcmil (.988 DIA.) 61 STR.; 750 kcmil CMPCT (.908 DIA.) 61 STR.; 700 kcmil (.964 DIA.) 61 STR.	750 kcmil (.988 DIA.) 61 STR.; 750 kcmil CMPCT (.908 DIA.) 61 STR.; 700 kcmil (.964 DIA.) 61 STR.	2.87 [73]	6.74 [171]	3"	3"	936
YRB44U31TW	1000 kcmil (1.152 DIA.) 61 STR.	350 kcmil (.681 DIA.) 37 STR. OR 350 kcmil CMPCT (.616 DIA.) 19 STR. ALUM.; 37 STR. ALUM. & CU.	2.87 [73]	6.74 [171]	3"	3"	936
YRB44U34TW	1000 kcmil (1.152 DIA.) 61 STR.	500 kcmil (.813 DIA.) 37 STR. OR 500 kcmil CMPCT (.736 DIA.) 19 STR. ALUM.; 37 STR. ALUM. & CU.	2.87 [73]	6.74 [171]	3"	3"	936
YRB44U39TW	1000 kcmil (1.152 DIA.) 61 STR.	750 kcmil (.988 DIA.) 61 STR.; 750 kcmil CMPCT (.908 DIA.) 61 STR.; 700 kcmil (.964 DIA.) 61 STR.	2.87 [73]	6.74 [171]	3"	3"	936
YRB44U44TW	1000 kcmil (1.152 DIA.) 61 STR.	1000 kcmil (1.152 DIA.) 61 STR.	2.87 [73]	6.74 [171]	3"	3"	936

COLOR CODE	INSTALLATION TOOLING (# OF CRIMPS PER END)						
	DIE INFORMATION		HYDRAULIC				
	DIE INDEX	TYPE	Y35, Y39, Y750 BAT35, BAT750 PAT750	Y46	Y45	Y48B	Y60BHU
YELLOW	936	YELLOW DIE SET	U39ART-2 (4)	U39ART-2 (4)	U39ART-2 (4)	C39AR-2 (2)	L39ART-2 (2)



TYPICAL LETTERING VIEW



NOTES:

- MATERIAL: ALUMINUM
- FINISH: HOT-TIN DIPPED.
- BARRELS ARE PARTIALLY FILLED WITH PENETROX™ AND SEALED.
- SCRATCH BRUSHING OF ALL CONDUCTORS BEFORE MAKING INSTALLATION IS RECOMMENDED
- NOT FOR USE WITH COPPER TO COPPER APPLICATIONS.
- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- CATALOG #PT6515 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y45 SERIES TOOLS.
- CATALOG #PUADP-1 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y46 SERIES TOOLS.
- INDEX NUMBER 936 GIVES A HEXAGONAL CRIMP.

REV.	DATE	DESCRIPTION	ECD	BY	C'K'D.
E	12/10/2015	FOCUS REQUEST PIN FPN1512018	42398	AV	MB

TO ORDER BURNDY® PRODUCTS CALL		HYREDUCERT™	
UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: N/A	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT NO: YRB- -U- -TW (TABLE)	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		SCALE: N/A	
		DRAWN BY: D BOISVERT 7/20/98	
		CHECKER: J MICHAUD 8/6/98	
		DSN APPVL: D WALTERS 7/13/98	
		MFG APPVL: --	
		QC APPVL: S GRAY 7/14/98	
		MKT APPVL: B HARGROOVE 7/14/98	
		DRAWING NO	
		SE211534	
		REV	
		E	
		SHEET 5 OF 5	