



CATALOG NO.	L
B4F8N	8.00 [203]
B4F10N	10.00 [254]
B4F10D50N	10.50 [267]
B4F12N	12.00 [305]
B4F15N	15.00 [381]
B4F16N	16.00 [406]
B4F16D50N	16.50 [419]
B4F18N	18.00 [457]
B4F20N	20.00 [508]
B4F21N	21.00 [533]
B4F24N	24.00 [610]
B4F28N	28.00 [711]
B4F30N	30.00 [762]
B4F38N	38.00 [965]
B4F44N	44.00 [1118]
B4F48N	48.00 [1219]
B4F54N	54.00 [1372]
B4F60N	60.00 [1524]
B4F72N	72.00 [1829]
B4F14N	14.00 [356]



**NOTES:**

- 1 FINISH: ADD CATALOG NUMBER FOLLOWED BY "TN" TO INDICATE TIN PLATED FERRULES.  
ADD CATALOG NUMBER FOLLOWED BY "W" TO INDICATE HOT TIN DIPPED FERRULES.  
ADD CATALOG NUMBER FOLLOWED BY "SV" TO INDICATE SILVER PLATED FERRULES.  
ADD CATALOG NUMBER FOLLOWED BY "NK" TO INDICATE NICKEL PLATED FERRULES.
2. APPROXIMATE AMP RATING: 1000 INDOOR, 1200 OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
3. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 4 ADD SUFFIX LETTER "U" AFTER "N" FOR UNDRILLED VERSIONS.  
EXAMPLES: B4F12NU OR B4F12NUTN
- 5 ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- 6 BRAID SIZES MAY BE DESIGNATED BY SUFFIXES REPRESENTING VARIATIONS IN LENGTH, QUANTITY & SIZE OF MOUNTING HOLES, PAD SIZE AND FINISH. (REF. NOTES 5).

TO ORDER BURNDY® PRODUCTS CALL  
UNITED STATES:  
1-800-346-4175 (LONDONDERRY, NH)  
CANADA:  
1-800-361-6975 (QUEBEC)  
1-800-387-6487 (ALL OTHER PROVINCES)  
FOR PRODUCT INFO: <http://www.burndy.com>

FLEXIBLE BRAID	
ITEM NO: N/A	
CAT NO: BF4-N (TABLE)	
SCALE: NTS	
DRAWN BY: B. MICHAUD	07/30/99
CHECKER: P. LAPONIUS	08/02/01
DSN APPV: R. LAVOIE	07/29/09
MFG APPV: T. WAWRZYNIAK	08/07/09
QC APPV: C. ACKERMAN	08/03/09
MKT APPV: ---	---
PROJ FAM: ---	---
PROJECT #: ---	---
DOCUMENT TYPE: Sales	
REL LEVEL: Released	
DRAWING NO	REV
SE212248-01	D
SHEET 1 of 1	

