

6



5

4

3

2

1



TOP AND BOTTOM FACES

REVISIONS					
ZONE	REV	DESCRIPTION	DRAWN BY:	DATE	APPR.
	A	Modifications a la geometrie de l'isolateur	SR	12/06/00	SR
	B	Rajout des dimensions	SR	22/09/00	SR
	C	Modif. Rayon R20	SR	12/10/00	SR
	D	Changement des inserts du haut à 50mm	SR	23/11/00	SR
	E	Complete update of drawing	SR	5/03/02	SR

Model		T208A
Physical Characteristics		
Height - in[mm]	14 [355±0.8]	
Major Diameter - in[mm]	6.9 [176±1.6]	
Head Diameter - in[mm]	4.7 [120±1.6]	
Weight - lbs[kg]	15.9 [7.3±0.2]	
Color	grey	
Electrical Properties		
BIL - kV	150	
Leakage Distance - in[mm]	37.13 [943±5]	
Dry Arc Distance - in[mm]	14.80 [376±2]	
No. of Sheds	11	
Minimum Mechanical Properties		
Compressive - lbs[kN]	10,000 [44.5]	
Cantilever - lbs[kN]	2,000 [8.9]	
Torsional - lbs-in[N-m]	8,000 [904]	
Tensile - lbs[kN]	10,000 [44.5]	

BOLT CIRCLE
3" [76.2]

NOTES:

- 1- SPECIFICATIONS IN ACCORDANCE WITH ANSI C29.9.
- 2- TESTED IN ACCORDANCE WITH ANSI C29.1.
- 3- MECHANICAL PROPERTIES ARE FOR BOLT PATTERN AS SHOWN.
- 4- BRASS INSERTS AVAILABLE UPON REQUEST.

This drawing is the proprietary property of Electro Composites Inc., not part of the public domain, and is issued with the express understanding and agreement that it is not to be reproduced or copied in whole or in part or issued for furnishing information to others, or used directly or indirectly, in any way detrimental to the interest of Electro Composites Inc. and is to be returned upon request by Electro Composites Inc. All Rights Reserved.

ITEM NO.	QTY	DRAWING NO.	PART NO.	DESCRIPTION	NOTE OR MAT'L
003	4	S-1001-955		INSERT 1/2-13 x 50mm de long	STEEL
002	4	S-1001-955		INSERT 1/2-13 x 50mm de long	STEEL
001	1	S-1001-696		BODY, CYCLOALIPHATIC RESIN	EPOXY
		-100		DRAWING NO.	

GENERAL TOLERANCES (UNLESS OTHERWISE SPECIFIED) X ±1.6 .X ±0.8 .XX ±0.4 .XXY ±.0001 ANGLES ±.1° RADIUS ±0.5 REMOVE BURRS AND BREAK SHARP EDGES DIMENSIONS ARE IN MILLIMETERS (UNLESS OTHERWISE SPECIFIED)	CUSTOMER --- DRAWN BY: S. RIOPEL DATE: 00/05/26 VER.: APP.: PROJECT ING.:		
		TITLE: OUTDOOR APPARATUS INSULATOR ANSI C29.9 - T208A	
FORMAT: A CAGE CODE: --- DWG. NO.: S-1001-696 REV.: E		SCALE: NONE GENERATED BY STRIM VERSION 5.3 PAGE 1 OF 1	

6

5

4

3

2

1