



CFB2G25 / CFB2G30 (RECTANGULAR COVER FOR 2 1/2" , 3" MIN POUR)




TOP VIEW

NOTES:

- 1. CFB2G30 SERIES SUPPLIED WITH RECTANGULAR COVER FOR 2 1/2 AND 3 INCH MIN. POUR.
- 2. CFB2G30R SERIES SUPPLIED WITH ROUND COVER FOR 3 1/4 AND 3 3/4 INCH MIN. POUR.
- 3. BOX TYPE WHICH INCLUDES STANDARDS, CORROSION-RESISTANT.
- 4. FOLLOW MANUFACTURERS DIRECTIONS AND GUIDELINES FOR THE INSTALLATION AND MOUNTING OF THE FLOOR BOX AND ALL OF THE ASSOCIATED COMPONENTS.



CFB2G25R / CFB2G30R (ROUND COVER FOR 3 1/4 ", 3 3/4" MIN POUR)



THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE

2 GANG RECESSED FLOOR BOX

TOLERANCES UNLESS OTHERWISE SPECIFIED
.XX = ± .01

 $.XXX = \pm .005$ ANGLES = $\pm 2^{\circ}$

HUBBELL INCORPORATED SHELTON, CT	
BY	APP. BY
D) (CCALE


DATE


DIMENSION SHEET FOR CAT. NO.

CFB2GXX,CFB2GXXR

W


G RECESSED FLOOR BOX






CFB2G25R / CFB2G30R (ROUND COVER OPEN)


SYSTEM ONE 2 GANG PLATES AND ACCESSORIES




CATALOG NO.	DESCRIPTION
FBMPREC	STYLELINE DECORATOR PLATE




CAT. No.	DESCRIPTION	
FBMPAAP	2-UNIT EXTRON AAP	




CAT. No.	DESCRIPTION
FBMPDUP	DUPLEX



CAT. No.	DESCRIPTION	
FBMP2IM	2-UNIT ISTATION®	



CAT. No.	DESCRIPTION
FBMPMAAP	EXTRON MAAP OR FR IPS



CAT. No.	DESCRIPTION	
FBMP15IM	1.5-UNIT ISTATION®	

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE

2 GANG RECESSED FLOOR BOX

TOLERANCES UNLESS
TOLERANCES UNLESS OTHERWISE SPECIFIED

 $.XX = \pm .01$ $.XXX = \pm .005$ $ANGLES = \pm 2$

SHELTON, CT	
DR. BY	APP. BY
TR. BY	SCALE
CHK BY	DATE

WIRING DEVICE-KELLEMS


DIMENSION SHEET FOR CALL NO.

CFB2GXX, CFB2GXXR


W

G RECESSED FLOOR BOX


SYSTEM ONE 2 GANG PLATES AND ACCESSORIES




CAT. No.	DESCRIPTION	DIM "A"
FBMP156	TWISTLOCK®	ø1.60 [40.5]
FBMP139	SIMPLEX OR TWISTLOCK ®	ø1.41 [35.7]




CAT. No.	DESCRIPTION
FBMPBNK	BLANK PLATE




CAT. No.	DESCRIPTION
FBMPFT	FEED THRU (INCLUDES BUSHING)




THERMOPLASTIC INSERT SUPPLIED



CAT. No.	DESCRIPTION	
FBMPTRAC	FOR TWO ORTRONICS TrackJack®OR ONE Series II® DATACOM INSERT	





CAT. No.	DESCRIPTION	
FBMP6KS	6-PORT KEYSTONE BEZEL	

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE

2 GANG RECESSED FLOOR BOX

TOLERANCES UNLESS OTHERWISE SPECIFIED	

 $.XX = \pm .01$ $.XXX = \pm .005$ TR. BY ANGLES = $\pm 2^{\circ}$

HUBBELL INCORPORATED SHELTON, CT		
DR. BY	APP. BY	
TR. BY	SCALE	
CHK. BY	DATE	

WIRING DEVICE-KELLEMS

CFB2GXX,CFB2GXXR


W

G RECESSED FLOOR BOX


THE FLOOR BOXES,COVERS AND SUB-PLATES ARE ALL UL514A & cULus LISTED. AVAILABLE IN PRE-WIRED PLATES WHICH REDUCES WIRING AND INSTALLATION TIMES FOR 15A AND 20A.

MOUNTING HARDWARE INCLUDED.


SYSTEM ONE 2 GANG RECTANGULAR COVER- SURFACE STYLE








24GCCVRXXC (WITH INSERT)




24GCFFCVRXX (FURNITURE FEED)


SYSTEM ONE 2 GANG RECTANGULAR COVER- FLUSH STYLE



24GTCVRXX (FLUSH)





24GTCVRXXC (WITH INSERT)



24GTFFCVRXX (FURNITURE FEED)

SYSTEM ONE 2 GANG ROUND COVER





CFBS1R6FFCVRXXX (FURNITURE)
CFBS1R6FFCVRBLK - BLACK
CFBS1R6FFCVRNKL - NICKEL

* FLOOR BOX ON THIS PAGE ARE AVAILABLE IN THE FOLLOWING COVER COLOR OPTION AS INDICATED BY THE CATALOG NUMBERS. ALU-ALUMINUM POWDER COAT, BK- BLACK POWDER COAT, BRS- BRASS POWDER COAT, BRZ- BRONZE POWDER COAT, NK- SATIN NICKEL POWDER COAT.

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE

2 GANG RECESSED FLOOR BOX

DR. BY

TR. BY

CHK. BY

TOLERANCES UNLESS OTHERWISE SPECIFIED

> $.XX = \pm .01$ $.XXX = \pm .005$ ANGLES = $\pm 2^{\circ}$

SHELTON, CT

APP. BY

SCALE

DATE

WIRING DEVICE-KELLEMS

HUBBELL INCORPORATED

DIMENSION SHEET FOR CAT. NO.

CFB2GXX, CFB2GXXR

REPAIRABLE

NON-REPAIRABLE

B

G

RECESSED

FLOOR BOX