




M-10800

6

CATALOG NO.	RATING	CONDUCTOR & CABLE RANGE	UL	CSA	PSE
CS6365L	50A 125/250V	8/3 +10/1 TO 4/4	YES	YES	NO
CS8365L	50A 250V 3Ø	.83-1.25 [21.1-31.8]	YES	YES	NO




CS8365L



NOTES: (UNLESS OTHERWISE SPECIFIED)

- DIMENSIONS IN INCHES [mm]
- TOLERANCES: ±.1

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
HOUSING	NYLON	
BLADE HOLDER	NYLON	
BLADE COVER	NYLON	
NUT	PBT	
SHROUD	STAIN. ST.	
DUST SHIELD	RUBBER	
BLADES	BRASS	
ASSY RIVITS	COPPER ALLOY	
DIVIDERS	POLYCARBONATE	
TERMINALS	ALUMINUM	TIN
TERMINAL SCREWS	STEEL	TIN
ASSY SCREWS	STEEL	ZINC
GROUND CONTACT	BRASS	
GROUND SHUNT	BRASS	



CATALOG NO. CS6365L
(NOT SHOWN TO SCALE)

6	REDRAWN WITH EMBEDDED CAD MODEL WITH NO CHANGES TO PART GEOMETRY. PER DCN 21895 SPN	DJP	2/5/16
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
PLUG

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLES = ± 2'	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT			
	DR. BY	PJT	APP. BY	MAM
	TR. BY		SCALE	1/2
	CHK. BY	TLS	DATE	12-23-08

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE NON-REPAIRABLE

B

M-10800

6