

RATED VOLTAGE: OPERATING VOLTAGE RANGE: CURRENT: FREQUENCY: TRIP LEVEL:

PHASE: RESPONSE TIME: DIELECTRIC WITHSTAND:

SURGE WITHSTAND:

OPERATING TEMPERATURE RANGE: -35 E LEAKAGE CURRENT @ 93% HUMIDITY: ZERO OVERLOAD CURRENT: RF NOISE SUSCEPTIBILITY:

LET GO LINE VOLTAGE: GROUNDED NEUTRAL DETECTION: 120VAC 85% TO 110% OF RATED

UP TO 20 AMPS 60Hz 5mA +/- ImA SINGLE

25 ms MAX. 1500 VRMS ACROSS CONTACT 4000 VRMS BETWEEN CONDUCTORS AND ENCLOSURE

6000V IMPULSE, 0.5 MICROSECOND RISE TIME 100KHZ RINGING FREQUENCY WITH 40% DECAY PER CYCLE -35 DEGREE CELSIUS TO +66 DEGREE CELSIUS

120 AMPS, 50% INDUCTIVE NORMAL OPERATION WITH 0.5 VRMS INJECTED ON POWER LINE WITH FREQUENCIES UP TO 450 MHz

60% OF RATED 6 OHMS OR LESS

U.L. AND CUL.


CONSTRUCTION: MOUNTING TYPE: WIRING APPLICATION: SWITCH INTERFACE: LATCHING MECHANISM:

FALSE TRIP DUE TO IMPACT:

AGENCY APPROVAL:

INDUSTRIAL GRADE DESIGN CONSTRUCTION: INDUSTRIAL GRADE DESIGN
TYPE: CLASS A
POWER-UP TYPE: AUTO AND MANUAL
OPEN NEUTRAL PROTECTION: TRIPS UPON LOSS OF NEUTRAL
GROUNDED NEUTRAL PROTECTION: TRIPS IF GROUND AND NEUTRAL CONNECT AT LOAD SIDE
POWER ON INDICATION: LIGHTED GREEN LED
POWER OFF INDICATION: BLINKING RED LED
ENCLOSURE: NEMA 4X
MOUNTAINS TYPE. PORTABLE 3 WIRE, SINGLE PHASE (HOT, NEUTRAL, GROUND)
DOUBLE INSULATED
ELECTROMAGNETIC

WARNING LABEL 2.52 64.0 12.00--12.00 6.00 304.8 [304.8] 152.3 LINE CABLE 12/3 SJTW UL LISTED 300V NEMA L5-20 OR L6-20 NEMA L5-20 OR L6-20-MOLDED PLUG BLACK MOLDED CONNECTOR BLACK



GFPIL20125LKA & GFPIL20250LKA AUTOMATIC RESET GFPIL20125LKM & GFPIL20250LKM MANAUL RESET

						ET FOR CAT. NO.
						REPAIRABLE [
כ י						NON-REPAIRABLE
	I INITIAL	RELEASE PE	ER DCN. 13040	J.	4-5-06	В
	SYM	REVISIO	MARKET CONTRACTOR AND ADDRESS OF THE PARTY O	APP	DATE	
	THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE					M - 1
	TITLE 20A. 120 & 240VAC 2 FT. GFC! ASSY. AUTO AND MANUAL RESET. NEMA L5-20 & L6-20					
	TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ± 1/84 OECIMALS ± .005 WIRING DEVICE-KELLENS HUBBELL INCORPORATED BRIDGEPORT, CT OR. BY TJV APP. BY SC					9
		± 2*	TR. BY	S	ALE NONE	
			CHK'D BY	D	TE 2-24-06	

LIST OF PARTS

MATERIAL

FINISH

DESCRIPTION

CODE 74545