

NOTES: (UNLESS OTHERWISE SPECIFIED):

1) DIMENSIONS ARE: INCHES [MM]

LOAD 1

LOAD 2


DPDT

WIRING

2) SUPPLIED ASSEMBLED WITH: KNURL NUT AND HEX NUT.

3) RECOMMENDED PANEL MOUNT OPENING 0.50 [12.7].

4) RATING: 10 AMP, 277VAC 20 AMP, 125VAC 1-1/2 HP, 125-250



CATALOG NO.	TERMINAL TYPE	SWITCH DESCRIPTION	PACKING
HBL22SP	SPADE, .250 MALE TAB NEMA	DOUBLE POLE, DOUBLE THROW	SINGLE PACK
HBL22SPM1	SPADE, .250 MALE TAB NEMA	DOUBLE POLE, DOUBLE THROW	BULK PACK 100 PCS.
HBL22	SCREW, #6-32UNS-2B	DOUBLE POLE, DOUBLE THROW	SINGLE PACK

LIST OF PARTS			2
DESCRIPTION	MATERIAL	FINISH	
			DANSISON SHEET FOR CAT. MOSEE TABLE
			_ H
			2
			, i
			1 H
			∃ ≒
			- E
			∃ ‴
			٦
			REPAIRABLE [
			8
			Fi
			z
			NON-REPAIRABLE
			曼
			暑
5. 6			FF
			⊠
1			
1 RELEASED FOR PE PER DCN # 13193.		JPP 8/31/06	
SYM REVISK		APP DATE	
THE DESIGN A	ND DIMENSIONS	OF THE	
	IN ON THIS DRA		12
SUBJECT TO C	HANGE WITHOUT	NOTICE	1
ITLE SEST	T0001 F 0::	//TOLL	76
	TOGGLE SW TAB TYPE TE		12
.200 WALL	•		M-10205
TOLERANCES UNLESS OTHERWISE SPECIFIED WIRING DEWCE-KELLENIS HUBBELL INCORPORATED			0
	BRIDGE	PORT, CT	
FRACTIONS ±1/64	DO BY INANI	APP RY IDD	_
	DR. BY JMN TR. BY	SCALE NONE	-

CODE 74545