













M-8310

6


MARINE CAT. NO.	CONFIGURATION	CENTER PIN	RATING	CAT. NO.	CONFIGURATION	CENTER PIN	RATING
HBL63CM70	 NEMA SS1-50R	NO	50A 125V 2-POLE 3-WIRE	CS6370		YES	50A 125V 2-POLE 3-WIRE
HBL63CM69	 NEMA SS2-50R	NO	50A 125/250V 3-POLE 4-WIRE	CS8269		YES	50A 250V 2-POLE 3-WIRE
				CS8469		YES	50A 480V 2-POLE 3-WIRE
				CS6369		YES	50A 125/250V 3-POLE 4-WIRE
				CS8369		YES	50A 250V 3-PHASE 3-POLE 4-WIRE
				CS8169		YES	50A 480V 3-PHASE 3-POLE 4-WIRE
				HBL3771		NO	50A 250VDC 50A 600VAC 2-POLE 3-WIRE
				HBL3769		NO	50A 250VDC 50A 600VAC 3-POLE 4-WIRE
				HHBL7379		NO	50A 250VDC 50A 600VAC 3-POLE 4-WIRE



NOTES:
 1. ON "CM" DEVICES, STEEL PARTS ARE MADE OF BRASS OR STAINLESS STEEL AND ALL BRASS PARTS ARE .0003 NICKEL PLATED.
 2. ALL DIMENSIONS TO BE INCHES [mm]

CODE 74545

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BODY	PHENOLIC	
END PIECE	PHENOLIC	
CENTER PIN	STEEL	Zn PLATE
CONTACT SPRINGS	BRASS	
TERMINAL	STEEL	Zn PLATE
TERMINAL	STEEL	GREEN FINISH
TERMINALS	STEEL	BRASS PLATE
SCREWS	STEEL	Zn PLATE
COVER	STEEL	Zn PLATE
BRIDGE	STEEL	Zn PLATE
INSULATOR	PHEOLIC	
RIVET	BRASS	Zn PLATE



CATALOG NO. CS6369
 (NOT SHOWN TO SCALE)

6	REDRAWN WITH EMBEDDED CAD MODEL WITH NO CHANGES TO PART GEOMETRY. PER DCN 21895 SPN	DJP	2/5/16
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
 50A TWIST LOCK RECEPTACLE

TOLERANCES UNLESS OTHERWISE SPECIFIED				WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT			
.XX = ± .01	.XXX = ± .005	ANGLES = ± 2'	DR. BY	DJH	APP. BY	MJR	
			TR. BY		SCALE	NONE	
			CHK. BY		DATE	10/5/94	

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE NON-REPAIRABLE

B

M-8310

6