




M-5983 1



CABLE CLAMP HOLDS
CABLE FROM $\varnothing .39$ [9.9]
TO $\varnothing .78$ [19.8]

CAT. NO.	CONFIGURATION	RATING
HBL8411C	NEMA 14-20P	20A. 125/250V
HBL8421C	NEMA 15-20P	20A. 250V 3 \varnothing
HBL7251C	NEMA 18-20P	20A. 120/208V. 3 \varnothing Y

NOTES: (UNLESS OTHERWISE SPECIFIED)

- 1) DIMENSION FORMAT IS: INCHES [mm]
- 2) DIMENSIONS SHOWN ON THIS DRAWING ARE NOMINAL VALUES FOR GENERAL USE ONLY. ACTUAL PART TOLERANCES MUST BE OBTAINED FROM HUBBELL ENGINEERING.

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BLADE HOLDER	NYLON	NATURAL
RETAINER	POLYCARBONATE	NATURAL
COVER	NYLON	BLACK
CORD CLAMP	NYLON	NATURAL
BLADES	BRASS	*
GROUND BLADE	BRASS	
TERMINAL PLATE	BRASS	
WIRE CLAMPS	STEEL	NICKEL PLATE
BINDING SCREWS	BRASS	*
CORD CLAMP SCREWS	STEEL	ZINC PLATE
FIL. HEAD SCREWS	STEEL	ZINC PLATE
DRIVE SCREW	STEEL	ZINC PLATE

* = WHITE FINISH ON NEUTRAL PARTS
WHEN USED

SUPERSEDES DRAWING
DATED 8-14-77

1 REDRAWN ON CAD WITH CHANGES; TCM 9/14/01
DECIMAL DIMENSIONS WERE
FRACTIONAL; ADDED DUAL
DIMENSIONING; ADDED NOTES
1 & 2; REVISED TITLE; COMBO
SCREWS WERE STRAIGHT BLADE;
PER DCN #8682.
JMN TCM

SYM REVISIONS APP DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
ANGLED PLUG

TOLERANCES UNLESS
OTHERWISE SPECIFIED
FRACTIONS $\pm 1/64$
DECIMALS $\pm .005$
ANGLES $\pm 2^\circ$

WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
BRIDGEPORT, CT
DR. BY ASM APP. BY JNC
TR. BY JMN SCALE FULL
CHK'D BY TCM DATE 9/14/01