



M-13470

1



10 FEET PER LENGTH	TRAY WIDTH	LOAD * (Lb/ft)	TRAY AREA (Sq. In.)	WEIGHT PER LENGTH (Lb)	SPLICE QUANTITY*		ROUND	
					90° SWEEP ELBOW	STRAIGHT SPLICE	TYPE 304L	TYPE 316L
2 [50.8] DEEP TRAY	4 [101.6]	45	8	7	2	2	HBT0204S04	HBT0204S16
	6 [152.4]	50	12	9	3	4	HBT0206S04	-
	8 [203.2]	52	16	10.5	4	4	HBT0208S04	HBT0208S16
	12 [304.8]	58	24	12	6	4	HBT0212S04	HBT0212S16
	16 [406.4]	70	32	15	7	4	HBT0216S04	-
	18 [457.2]	70	36	23	9	4	HBT0218S04	-
	24 [609.6]	75	48	31	12	5	HBT0224S04	-
4 [101.6] DEEP TRAY	4 [101.6]	49	16	12	2	4	HBT0404S04	-
	6 [152.4]	49	24	13	3	5	HBT0406S04	HBT0406S16
	8 [203.2]	78	32	15	4	6	HBT0408S04	-
	12 [304.8]	78	48	23	6	6	HBT0412S04	HBT0412S16
	16 [406.4]	108	64	27	7	7	HBT0416S04	-
	18 [457.2]	116	72	29	9	7	HBT0418S04	-
	24 [609.6]	116	96	35	12	8	HBT0424S04	-
6 [152.4] DEEP TRAY	8 [203.2]	116	48	23	4	6	HBT0608S04	-
	12 [304.8]	123	72	27	6	6	HBT0612S04	HBT0612S16
	16 [406.4]	123	96	31	7	7	HBT0616S04	-
	20 [508.0]	127	120	35	9	7	HBT0620S04	-
	24 [609.6]	150	144	39	12	8	HBT0624S04	-
8 [203.2] DEEP TRAY	8 [203.2]	116	64	27	4	8	-	-
	12 [304.8]	116	96	31	6	8	-	-
	16 [406.4]	116	128	35	7	9	-	-
	18 [457.2]	116	144	37	9	9	-	-
	20 [508.0]	116	160	39	9	9	-	-

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
TRAY	STAINLESS STEEL	NATURAL




CATALOG NO. HBT0412S04 (NOT SHOWN TO SCALE)

1	INITIAL DOCUMENT	DDL	11/15/16
	RELEASE PER DCN 22750		
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE
STAINLESS STEEL WIRE BASKET TRAY



TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2'	DR. BY GM	SCALE NONE
	CHK. BY MN	DATE 08/16/16

- NOTES:**
1. TYPE 304L AND 316S STAINLESS STEEL MEETS ASTM A580 SPECIFICATIONS
 2. STAINLESS SPLICE KITS AND CEILING SUPPORTS ARE AVAILABLE
 3. * SUPPORTED AT SIX FOOT SPACING
 4. ALL DIMENSIONS ARE ±.25 [6.3]
 5. 2 X 4 [50.8 X 101.6] MESH OPENING