


M-13486

1

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BASE	STEEL	PRE-GLAVANIZED OR PAINT
WALLS	POLYMER	BLACK
HARDWARE	STEEL	ZINC PLATED


DIMENSION SHEET FOR CAT. NO. SEE TABLE




INSIDE WALL



OUTSIDE WALL



TRAY SIZE "D"	TRAY WIDTH "W"	TRAY AREA (Sq. In.)	PRE-GALVANIZED	BLACK POWDER COAT
2 [50.8] DEEP	4 [101.6]	8	HBTR0204	HBTR0204BK
	6 [152.4]	12	HBTR0206	HBTR0206BK
	8 [203.2]	16	HBTR0208	HBTR0208BK
	12 [304.8]	24	HBTR0212	HBTR0212BK
	16 [406.4]	32	HBTR0216	HBTR0216BK
	18 [457.2]	36	HBTR0218	HBTR0218BK
	20 [508.0]	40	HBTR0220	HBTR0220BK
	24 [609.6]	48	HBTR0224	HBTR0224BK
4 [101.6] DEEP	4 [101.6]	16	HBTR0404	HBTR0404BK
	6 [152.4]	24	HBTR0406	HBTR0406BK
	8 [203.2]	32	HBTR0408	HBTR0408BK
	12 [304.8]	48	HBTR0412	HBTR0412BK
	16 [406.4]	64	HBTR0416	HBTR0416BK
	18 [457.2]	72	HBTR0418	HBTR0418BK
	20 [508.0]	80	HBTR0420	HBTR0420BK
	24 [609.6]	96	HBTR0424	HBTR0424BK
6 [152.4] DEEP	8 [203.2]	48	HBTR0608	HBTR0608BK
	12 [304.8]	72	HBTR0612	HBTR0612BK
	16 [406.4]	96	HBTR0616	HBTR0616BK
	18 [457.2]	108	HBTR0618	HBTR0618BK
	20 [508.0]	120	HBTR0620	HBTR0620BK
	24 [609.6]	144	HBTR0624	HBTR0624BK



CATALOG NO. HBTR0212
(NOT SHOWN TO SCALE)

1	INITIAL DOCUMENT	DDL	11/15/16
	RELEASE PER DCN 22750		
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE
PRE-FORMED 90 DEGREE FITTING

HUBBELL WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ±.01 .XXX = ±.005 ANGLE TOL. ±2'	DR. BY GM	SCALE NONE
	CHK. BY MN	DATE 09/07/16

NOTES:
1. MOUNTING HARDWARE INCLUDED