





M-11797 2



DIMENSIONS ARE INCHES (mm)



WIRE STRIP LENGTH



NOTES: UNLESS OTHERWISE SPECIFIED:

1. WIRE SIZE: 18AWG (0.75mm<sup>2</sup>) MAX.
2. ENCLOSURE RATING: IP67
3. OPERATING TEMPERATURE: -40° C TO 88° C.
4. **cus** RECOGNIZED.
5. RECOMMENDED REAR NUT TORQUES  
F7 STYLE - 7-8 IN.LBS (80-100 Ncm)  
F9 STYLE - 7-8 IN.LBS (80-100 Ncm).
6. RECOMMENDED TERMINAL TORQUE  
3.54 IN.LBS (40Ncm)

CATALOG NO.	POLES	RATING	CABLE RANGE
MCMA14F7	4	250V/4A	0.16-0.24 IN.
MCMA14F9	4	250V/4A	0.24-0.32 IN.
MCMA15F7	5	125V/4A	0.16-0.24 IN.
MCMA15F9	5	125V/4A	0.24-0.32 IN.

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
COUPLING NUT	BRASS	NICKEL PLATED
CONNECTOR SHELL	NYLON	BLACK
CONTACTS	BRASS	GOLD PLATED
		PALLADIUM
		NICKEL

2 12/21/10 CHANGE RATING FROM 250V TO 125V MICRO 5P REVERSED INCHES (mm) PER DCN 17339 CAC

1 12/1/10 NEW RELEASE PER DCN 17341 CAC

SYM	REVISIONS	APP	DATE
-----	-----------	-----	------

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE ANGLED FEMALE MICRO QUICK THD. TYPE F7, F9

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLENS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ±1/64	DR. BY CAC	APP. BY
DECIMALS ±.005	TR. BY	SCALE NONE
ANGLES ±2°	CHK'D BY	DATE 12-2-10

CODE 74545

DIMENSION SHEET FOR CAT. NO. SEE TABLE REPAIRABLE  NON-REPAIRABLE  B M-11797 2