


M12551 4



NOTES:
1. ALL DIMENSIONS ARE IN INCHES [mm].

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
COVER	THERMOPLASTIC	COLOR PER CAT#
BASE	THERMOPLASTIC	YELLOW
STRAP	GALV. STEEL	
TERMINAL	BRASS	
MOUNTING SCREW	STEEL	Zn PLATE
DRIVE STREW	STEEL	Zn PLATE
LINE SCREW	STEEL	BRASS PLATE
NEUTRAL SCREW	STEEL	Zn PLATE
GR. SCREW	STEEL	Zn PLATE + GREEN

SYM	REVISIONS	APP	DATE
4	UPDATED DRAWING PER DCN 23671 SBW		6/11/18
3	UPDATE THE PRINT PER DCN #21107		03/17/15
2	BASE COLOR YELLOW WAS BLACK PER DCN #20927		12/10/14
1	NEW RELEASE PER DCN #20652		08/19/14

SYM	REVISIONS	APP	DATE
4	UPDATED DRAWING PER DCN 23671 SBW		6/11/18
3	UPDATE THE PRINT PER DCN #21107		03/17/15
2	BASE COLOR YELLOW WAS BLACK PER DCN #20927		12/10/14
1	NEW RELEASE PER DCN #20652		08/19/14

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
RECESS TR DUP RCPT, 15A 125V

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
.XX = ± .01	.XXX = ± .005	DR. BY	N.H
ANGLES = ± 2°		APP. BY	SM
		TR. BY	N.H
		SCALE	1:1
		CHK. BY	C.Z
		DATE	06/04/2014

CAT#	DESCRIPTION	RATING	COLOR
RR1510LA	RECESS TR DUPLEX RECEPTACLE, 15A, 125V	15A 125V	LIGHT ALMOND
RR1510I			IVORY
RR1510W			WHITE
RR1510			BROWN
RR1510GY			GRAY
RR1510BK			BLACK

DIMENSION SHEET FOR CAT. NO.

SEE TABLE

REPAIRABLE

NON-REPAIRABLE

B

M12551 4