


M12562 4



NOTES:
 1. ALL DIMENSIONS ARE IN INCHES [mm].
 2. TO BE USED WITH HUBBELL BOX
 CAT.# RR1500 OR HBL985 & HBL989.

CATALOT NO:	DESCRIPTION	RATING	COLOR:
RR1514LA	2G RECESS TR DUPLEX RECEPTACLE W/SNAPFIT, 15A, 125V	15A, 125V	LIGHT ALMOND
RR1514I			IVORY
RR1514W			WHITE
RR1514			BROWN
RR1514GY			GRAY

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
COVER	THERMOPLASTIC	COLOR PER CAT#
BASE	THERMOPLASTIC	YELLOW
STRAP	GALV. STEEL	
MOUNTING SCREW	STEEL	Zn PLATE
DRIVE SCREW	STEEL	Zn PLATE
NEUTRAL SCREW	STEEL	Zn PLATE
LINE SCREW	STEEL	BRASS PLATE
GR. SCREW	STEEL	Zn PLATE + GREEN
TERMINAL	BRASS	

SYM	REVISIONS	APP	DATE
4	UPDATED DRAWING PER DCN 23671 SBW		6/11/18
3	UPDATE THE PRINT PER DCN #21107		03/17/15
2	BASE COLOR YELLOW WAS BLACK PER DCN #20927		12/10/14
1	NEW RELEASE PER DCN #20652		08/19/14

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
 2G RECESS TR DUP RCPT W/SNAPFIT, 15A 125V

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
.XX = ± .01	.XXX = ± .005	DR. BY N.H	APP. BY SM
ANGLES = ± 2°		TR. BY N.H	SCALE 1/2
		CHK. BY C.Z	DATE 06/03/2014

DIMENSION SHEET FOR CAT. NO. **M12562** **4**
 REPAIRABLE NON-REPAIRABLE