


M-10810 | 1



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
COVER	PLASTIC	
DRIVE SCREW	STEEL	ZINC
BASE	PLASTIC	
BRIDGE	STEEL	ZINC
TERM ASSY NEUTRAL	BRASS	
TERM ASSY HOT	BRASS	
SCREW	SS	
WASHER	PLASTIC	
GROUNDING SPRING	SS	
MOUNTING SCREW	STEEL	ZINC
TR ASSEMBLY	PLASTIC	

DIMENSION SHEET FOR CAT. NO. SEE TABLE REPAIRABLE NON-REPAIRABLE

SYMBOL	REVISIONS	APP	DATE
1	10/30/07 RELEASED TO PRODUCTION PER DCN# 14354	DMP	10/30/07

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
WR/TR 125V
SINGLE RECEPTACLE

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT.	
FRACTIONS	: 1/64	DR. BY	DMP
DECIMALS	: .005	APP. BY	
ANGLES	: 2°	TR. BY	
		SCALE	1:1
		CHK'D BY	DATE 10/30/07

CATALOG NO'S	COLOR	CONFIG	RATING
RR151WRTR	BROWN	NEMA 5-15R	15A 125V
RR151WRTR	IVORY		
RR151WRTR	WHITE		
RR151GYWRTR	GRAY		
RR151BKWRTR	BLACK		
RR151ALWRTR	ALMOND		
RR151LAWRTR	LIGHT ALMOND		
RR201WRTR	BROWN	NEMA 5-20R	20A 125V
RR201WRTR	IVORY		
RR201WRTR	WHITE		
RR201GYWRTR	GRAY		
RR201BKWRTR	BLACK		
RR201ALWRTR	ALMOND		
RR201LAWRTR	LIGHT ALMOND		

NOTE:
1) #14 AWG TO #10 AWG SOLID AND OR STRANDED COPPER WIRE ONLY
2) DIM'S ARE IN INCHES [MM].

M-10810