


M-8650|2



NOTES:

1. LAST 2 DIGITS OF CATALOG NUMBER SIGNIFY APPROXIMATE LENGTH (IN FEET) OF CABLE, AS DENOTED BY DIMENSION "A".  
(EXAMPLE: FOR CATALOG NUMBER SCC06, DIMENSION "A" IS 6 FEET)

CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	NYLON	
GASKET	RUBBER	
LOCK RING	POLYESTER	
INTERIOR	THERMOSET	
PINS	BRASS	
SLEEVES	BRASS	
TERMINAL SCREWS	ST. STEEL	
GLAND CAP	POLYESTER	
GLAND	RUBBER	
CORD CLAMPS	POLYESTER	
CLAMP NUTS	BRASS	NICKEL
ASSEMBLY SCREWS	ST. STEEL	
CABLE	COPPER	

DIMENSION SHEET FOR CAT. NO. SCC06, SCC07, SCC08... SCC50 REPAIRABLE  NON-REPAIRABLE

2	ADDED NOTE AND DIM. "A" DCN#9145-8	RDK	4/22/02
1	RELEASE PER DCN#9145-2	RDK	2/4/02
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE 60A 3ØY 120/208 VAC  
4 WIRE CABLE SET FOR  
60A SPIDER BOX

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ±1/64	DECIMALS ±.005	DR. BY PJT	APP. BY RDK
ANGLES ±2°		TR. BY	SCALE 1:4
		CHK'D BY RDK	DATE 2/4/02

**B**  
 M-8650  
**2**