



ITEM NO.	DESCRIPTION	QTY.		CATALOG NUMBER	DESCRIPTION
1	8 PORT TELEPHONE MODULE	1		NSOPTM8	8 PORT TELEPHONE MODULE
2	INSTRUCTION SHEET (NOT SHOWN)	1			



- NOTES:
1. FCC PART 68 COMPLIANT
 2. TIA 568-A WIRED
 3. ENVIRONMENTAL CONDITIONS
TEMPERATURE RANGE
STORAGE -40 TO +70°C
OPERATION -10 TO +60°C
 4. ELECTRICAL
ELECTRICAL INSULATION RESISTANCE: 500 MΩ MIN. @ 100V D.C.
DIELECTRIC WITHSTANDING VOLTAGE: 1000V D.C OR A.C. PEAK CONTACT @60HZ FOR 1 MINUTE
SPRING WIRE CONTACT RESISTANCE: 20 mΩ MAX.
IDC CONTACT RESISTANCE: 2.5 mΩ MAX.
CURRENT RATING: AS FIGURE
 5. COLOR BLACK WITH WHITE SILK-SCREEN.
 6. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.



Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°	PROJECT REFERENCE: 2008-009
		MATERIAL: BRACKET: ABS PLASTIC UL 94-V0
		DRAWN BY: B MARTINO 01/24/08
		CHECKED BY:
		APPROVED BY:
A 6270 01/24/08	INITIAL RELEASE	SIZE B DRAWING NO. HWS12631C REV. A
REV. ECN DATE	DESCRIPTION	SCALE: N/A SHEET 1 OF 1

HUBBELL Premise Wiring
HUBBELL INCORPORATED (Delaware)
14 Lord's Hill Road, Stonington, Connecticut 06378

TITLE: SOHO 8 PORT PRIMARY TELEPHONE MODULE