


CATALOG NUMBER	SIDE RAIL HEIGHT (in [mm])	WIDTH (in [mm])	LOAD DEPTH (in [mm])	LOAD (Lb/ft)	FITTINGS CLASS	FITTINGS PREFIX	AREA (Sq. In.)	AMP RATING	NEMA LOAD CLASS	CSA LOAD CLASS
LTB412	4 [101.6]	12 [304.8]	3 [76.2]	81	1	A41	.60	1000	12B	C
LTB418	4 [101.6]	18 [457.2]	3 [76.2]	81	1	A41	.60	1000	12B	C
LTB424	4 [101.6]	24 [609.6]	3 [76.2]	81	1	A41	.60	1000	12B	C
LTC412	4 [101.6]	12 [304.8]	3 [76.2]	100	1	A41	.60	1000	12C	D-3M
LTC418	4 [101.6]	18 [457.2]	3 [76.2]	100	1	A41	.60	1000	12C	D-3M
LTC424	4 [101.6]	24 [609.6]	3 [76.2]	100	1	A41	.60	1000	12C	D-3M
LTB612	6 [152.4]	12 [304.8]	5 [127.0]	89	1	A61	1.00	1200	12B	C
LTB618	6 [152.4]	18 [457.2]	5 [127.0]	89	1	A61	1.00	1200	12B	C
LTB624	6 [152.4]	24 [609.6]	5 [127.0]	89	1	A61	1.00	1200	12B	C
LTC612	6 [152.4]	12 [304.8]	5 [127.0]	105	1	A61	1.00	1200	12C	D-3M
LTC618	6 [152.4]	18 [457.2]	5 [127.0]	105	1	A61	1.00	1200	12C	D-3M
LTC624	6 [152.4]	24 [609.6]	5 [127.0]	105	1	A61	1.00	1200	12C	D-3M

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
TRAY	ALUMINUM 6063-T6	
HARDWARE	GEOMET PLATED STEEL	

1			
REV	DESCRIPTION	APP	DATE
	THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].		
	TITLE		
	ALUMINUM LADDER TRAY		
	 WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT		
	TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2'	DR. BY AD	SCALE 3/16
		CHK. BY	DATE 2/1/21

- NOTES:  
 1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS].  
 2. PRODUCT IS cULus LISTED.  
 3. LENGTH OF LADDER TRAY IS 12 ft (3.66 m).