



M-12150 1



NOTES: (UNLESS OTHERWISE SPECIFIED)

1. ALL DIMENSIONS ARE IN INCHES [mm].
2. CONTROL TYPE: THE LIGHTS WILL AUTOMATICALLY TURN ON WHEN THE SPACE IS OCCUPIED AND THERE IS NOT SUFFICIENT DAYLIGHT AVAILABLE. THE SENSOR WILL AUTOMATICALLY TURN THE LIGHTS OFF 15 MINUTES AFTER SUFFICIENT DAYLIGHT IS AVAILABLE IN THE SPACE. THE LIGHTS WILL AUTOMATICALLY TURN OFF WHEN THE SPACE IS VACANT.
3. OPERATING POWER SOURCE: 3 VDC 7 mA.
4. OPERATING FREQUENCY: 434 MHz.
5. ENVIRONMENT: FOR INDOOR USE ONLY, TEMP. 32 °F ~ 104 °F (0 °C ~ 40 °C) 0~95% HUMIDITY, NON-CONDENSING.
6. EACH SENSOR CAN BE ADDED TO RF SWITCHING DEVICES FOR SPACES WITH MULTIPLE ZONES OF LIGHTING.

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
TOP	POLYESTER	
BOTTOM	POLYESTER	
PCB	EPOXY RESIN	
SCREW	STEEL	Zn PLATE

1	NEW RELEASE PER DCN #18801	DL	DL	4/18/12
SYM	DESCRIPTION	APPRO	DATE	

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE DAYLIGHT SENSOR, CEILING MOUNT

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ±1/64 DECIMALS ±.005 ANGLES ±2°	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT			
	DR. BY	DL	APP. BY	SYA
	TR. BY		SCALE	2:1
	CHK'D BY	SYA	DATE	2/1/2012

DIMENSION SHEET FOR: CMT. NO. WLDH REPAIRABLE NON-REPAIRABLE B M-12150 1