


M-12340

4



(6) #14 AWG WIRES, TWO CIRCUITS
 A CIRCUIT: BLACK, WHITE, GREEN
 B CIRCUIT: RED, GRAY, GREEN/YELLOW

NOTES:

1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS].
2. PRODUCT IS cULus LISTED.
3. MOUNTING HARDWARE INCLUDE
4. SEE INSTALLATION INSTRUCTIONS FOR APPLYING CONTROLLED STICKER.

CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
COVER PLATE	STEEL	WHITE
RECEPTACLE	THERMOPLASTIC	BLACK
CONTACTS	COPPER ALLOY	NONE
FASTENERS	STEEL	ZINC
BRACKET	STEEL	ZINC
MOUNTING SCREWS	STEEL	WHITE

4	DELETED TABLE w/ #4 FLAG, IN NOTES- DELETED FLAG FOR NOTE 4, DELETED 'S1R4SPQUAD SHOWN' FOR VIEWS; IN DESCRIPTION SHEET, S1R4SPQUAD WAS SEE TABLE PER DCN 24352 RM	DJP	10/25/2018
3	ADDED TABLE, ADDED NOTE 4, ADDED BASE CATALOG NUMBER SHOWN PER DCN 21884 MYA	DJP	3/16/2016
2	REDRAWN PER DCN 21283	SBW	6/16/2015
SYM	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
 RECEPTACLE / COVER ASSEMBLY
 4 INCH RECESSED FRPT & FLOOR
 BOXES

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT.	
.XX = ± .01	DR. BY	SBW	APP. BY
.XXX = ± .005	TR. BY	SCALE	1/2
ANGLES = ± 2°	CHK'D BY	DATE	6/10/2015

DIMENSION SHEET FOR CAT. NO. S1R4SPQUAD
 REPAIRABLE NON-REPAIRABLE
 B
 M-12340
 4