


M-14467

1




AMP RATING PER N.E.C. 250	CABLE SIZE	CABLE TYPE	INSULATION COLOR
600	#1	THHN	GREEN

NOTES:

1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS].
2. FASTENERS ARE SUPPLIED SEPARATELY.
3. INSTALL IN ACCORDANCE WITH NEMA STANDARD VE-2 "CABLE TRAY INSTALLATION GUIDELINES".

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
LUGS	COPPER	TIN PLATED
WIRE	COPPER	

1	RELEASED PER DCN211102014008	AD	11/2/21
REV	DESCRIPTION	APP	DATE
THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].			
TITLE  COPPER BONDING JUMPERS, LADDER TRAY			
		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2°		DR. BY AD	SCALE 1 / 2
		CHK. BY SBW	DATE 10/13/21