


M-13400


2





SHAFT SHOULD BE ORIENTED VERTICALLY IN ORDER TO MATE WITH HANDLE IN THE 'OFF' POSITION.

SWITCH TERMINAL CABLE CONNECTION = TORQUE TO 275 IN-LBS [31 N-m]
3/8" MOUNTING HARDWARE = TORQUE TO 160 IN-LBS [18 N-m]

GROUND TERMINAL CABLE CONNECTION = TORQUE TO 275 IN-LBS [31 N-m]
1/2" MOUNTING HARDWARE = TORQUE TO 72 IN-LBS [8 N-m]



COVER NOT SHOWN FOR CLARITY




NOTES:

- ENCLOSURE RATINGS - UL TYPE 4X
- PRODUCT RATING - LISTED TO UL STANDARD 98

CAGE CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
ENCLOSURE	F.R. POLYESTER	-
HANDLE	PLASTIC	RED/YELLOW
SWITCH	PLASTIC	-
BACKPLATE	12 GA. ALUM.	NONE
TERMINALS	ALUMINUM	TIN PLATED
FASTENERS	STEEL	ZINC PLATED



CATALOG NO. HBLDS20
(NOT TO SCALE)

REV	DESCRIPTION	APP	DATE
2	MODIFIED PRODUCT LABEL LOCATION PER DCN# 22731		11/30/16
1	NEW DRAWING RELEASED FOR PRODUCTION PER DCN# 22326		8/2/16

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE

200A DISCONNECT, NON-METALLIC



WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED
.XX = ±.01
.XXX = ±.005
ANGLE TOL. ±2

DR. BY MS
CHK. BY TLS

SCALE 1/5
DATE 7/26/16

DIMENSION SHEET FOR CAT. NO. HBLDS20

B

M-13400

2