






M-9917 1



NOTES: (UNLESS OTHERWISE SPECIFIED)
 1. AWG CAPACITY: #4-#10
 2. FOR USE WITH ALUMINUM AND COPPER WIRE SOLID OR STRANDED
 3. DIMENSIONS ARE IN INCHES (MM).

CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
WIRE BASE PLATE	STEEL	ZINC
CORD CLAMPS	STEEL	ZINC
CONTACT BLADES	BRASS	
CONTACT SPRING 50A	BRASS	
CONTACT BASE	PLASTIC	
COVER	PLASTIC	
SCREWS	STEEL	ZINC

1	RELEASE PER DCN# 13429	11/27/06
SYM	REVISIONS	APP DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
 SURFACE MOUNT RECEPTACLE
 NEMA 10-50R

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT.
FRACTIONS ±1/64	DR. BY MPF
DECIMALS ±.005	TR. BY
ANGLES ±2°	CHK'D BY
	APP. BY
	SCALE 1/1
	DATE 10/3/05

DIMENSION SHEET FOR CAT. NO. RR350

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-9917 1