




M-3081 2



NOTES: (UNLESS OTHERWISE SPECIFIED)

- 1) DIMENSION FORMAT IS: INCHES [mm]
- 2) DIMENSIONS SHOWN ON THIS DRAWING ARE NOMINAL VALUES FOR GENERAL USE ONLY. ACTUAL PART TOLERANCES MUST BE OBTAINED FROM HUBBELL ENGINEERING.

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BODY	BAKELITE	BROWN
MOUNTING PLATE	.040 C.R.S.	ZINC PLATE
WIRE CLAMP	.083 C.R.S.	NICKEL PLATE
BINDING SCREWS	STEEL	NICKEL PLATE
CONTACT SPRINGS	.040 BRASS	*
INSULATOR	.125 FIBRE	

* = WHITE FINISH ON NEUTRAL PARTS WHEN USED

SUPERSEDES DRAWING DATED 5-23-66

2	REDRAWN ON CAD WITH CHANGES; DECIMAL DIMENSIONS WERE FRACTIONAL; ADDED DUAL DIMENSIONING; ADDED NOTES 1 & 2; REVISED TITLE; IN PARTS LIST, "NICKEL PLATE" WAS "CAD PL." ADDED " = WHITE FINISH ON NEUTRAL PARTS WHEN USED"; REMOVED HUBBELL GLOBE FROM INSULATOR PER DCN #8682. JMN TCM	TCM	10/16/01
---	---	-----	----------

SYM	REVISIONS	APP	DATE
-----	-----------	-----	------

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
RECEPTACLE, 30A. 125/250V.
NEMA 10-30R

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ±1/64	DR. BY RDT	APP. BY JNC
DECIMALS ±.005	TR. BY JMN	SCALE FULL
ANGLES ±2°	CHK'D BY ASM	DATE 10/16/01